

# iTHERM TM401

## Modular RTD thermometer - basic technology

For standard hygienic and aseptic applications in the Food & Beverages and Life Sciences industries

**F L E X**

### Benefits:

- Excellent value for money and fast delivery
- User-friendly and reliable from product selection to maintenance
- International certification: hygiene standards as per 3-A®, EHEDG, ASME BPE, FDA, TSE Certificate of Suitability
- Wide range of process connections

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751
- **Response time** depending on configuration
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi)
- **Operating temperature range** PT100: -50 °C ... 200 °C (-58 °F ... 392 °F)
- **Max. immersion length on request** up to 400 mm (15,75")

from **\$109.00**

Price as of 04/23/2021

More information and current pricing:

[www.us.endress.com/TM401](http://www.us.endress.com/TM401)

**Field of application:** This iTHERM thermometer has been designed to meet the basic requirements of the Food & Beverages and Life Sciences industries at the best price. It offers a variety of versions within a clearly segmented standard product. The result: Time and cost savings by simple and fast product selection. The device uses basic technology with features such as a fixed, non-replaceable insert, a wide range of process connections and international certification at an excellent value for money.

### Features and specifications

---

## Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Characteristic / Application**

metric style

hygienic applications

aseptic applications

hygienic process connections

with neck

---

**Thermowell / protection tube**

without (not intended to use with thermowell)

---

**Insert / probe**

without exchangeable insert

---

**Outer diameter protection tube / Insert**

6,0 mm (0,24")

8,0 mm (0,31")

---

**Max. immersion length on request**

up to 400 mm (15,75")

---

**Material protection tube/ thermowell**

316L

---

---

**Thermometer****Process connection**

compression fitting

triclamp

microclamp

clamp connections acc. to ISO2852

Ingold

G3/4" Liquiphant

G1" Liquiphant

Varivent

SMS 1147

screwed pipe joint acc. to DIN 11851

---

**Tip shape**

straight

reduced

---

**Surface roughness Ra**0,76  $\mu\text{m}$  (30  $\mu\text{in}$ )0,38  $\mu\text{m}$  (15  $\mu\text{in}$ )

---

**Operating temperature range**

PT100:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

## Thermometer

**Max. process pressure (static)**

at 20 °C: 40 bar (580 psi)

---

**Accuracy**

class A acc. to IEC 60751

---

**Response time**

depending on configuration

---

**Integration head transmitter**

yes (4 ... 20 mA, HART)

---

**Certification**

SIL (transmitter only)

---

More information [www.us.endress.com/TM401](http://www.us.endress.com/TM401)