

# TC63

## Explosion-proof TC thermometer with imperial thermowell

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



More information and current pricing:

[www.us.endress.com/TC63](http://www.us.endress.com/TC63)

### Benefits:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of insert compatibility and design as per DIN 43772
- Extension neck, nipple union version, to protect the head transmitter from overheating
- Variable selection of process connections: thread, compression fitting or flange
- Optionally fast response time with tapered tip form
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths

### Specs at a glance

- **Accuracy** class 1 acc. to IEC 60584
- **Response time** depending on configuration  $t_{50} = 3 \text{ s}$   $t_{90} = 7 \text{ s}$
- **Max. process pressure (static)** at 20 °C: 100 bar (1.450 psi)
- **Operating temperature range** Type K: -40 °C ... 1.100 °C (-40 °F ... 2.012 °F) Type J: -200 °C ... 750 °C (-328 °F ... 1.382 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Field of application:** The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials. An optional head transmitter with all common

communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. Flexible configuration possible.

## Features and specifications

---

### Thermometer

**Measuring principle**

Thermocouple

---

**Characteristic / Application**

US style

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

with neck

incl. thermowell / protection tube (metal)

---

**Thermowell / protection tube**

welded protection tube

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

1/4" SCH80

1/2" SCH80

1/2" SCH40

3/4" SCH80

3/4" SCH40

Thermometer

---

**Max. immersion length on request**  
 up to 10.000,00 mm (393,70")

---

**Material protection tube/ thermowell**  
 1.4401 (316)

1.4749 (~446)

---

**Optional coating**  
 Not defined

---

## Thermometer

**Process connection**

male thread:

NPT1/2"

NPT3/4"

NPT1"

compression fitting:

flange:

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

ASME 1" 600 RF (B16.5)

ASME 1,5" 150 RF (B16.5)

ASME 1,5" 300 RF (B16.5)

ASME 1,5" 600 RF (B16.5)

ASME 2" 300 RF (B16.5)

ASME 2" 600 RF (B16.5)

---

**Tip shape**

straight

reduced

---

**Surface roughness Ra**1,6  $\mu\text{m}$  (63,0  $\mu\text{in.}$ )

---

## Thermometer

**Operating temperature range**

Type K:

-40 °C ... 1.100 °C

(-40 °F ...2.012 °F)

Type J:

-200 °C ...750 °C

(-328 °F ...1.382 °F)

---

**Max. process pressure (static)**

at 20 °C: 100 bar (1.450 psi)

---

**Accuracy**

class 1 acc. to IEC 60584

---

**Response time**

depending on configuration

t50 = 3 s

t90 = 7 s

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

Thermometer

**Ex - approvals**

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

---

**Certification**

Gost Metrology

SIL (transmitter only)

---

More information [www.us.endress.com/TC63](http://www.us.endress.com/TC63)