

Absolute and gauge pressure Cerabar PMC71

Digital pressure transmitter with oil-free ceramic sensor for measurement in gases or liquids



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/PMC71

Lợi ích:

- Best fit for vacuum applications and applications with corrosive and abrasive media
- Process safety through membrane breakage detection
- Overload-resistant high purity ceramic sensor (99.9% Al₂O₃)
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Easy menu-guided commissioning via local display, 4 to 20mA with HART, PROFIBUS PA, FOUNDATION Fieldbus
- Highest safety due to gastight feedthrough with capabilities up to SIL2/3, certified to IEC 61508
- Available with mounted manifolds: always fit, always tested for leaks

Tổng quan về thông số kỹ thuật

- **Accuracy** 0,075% "PLATINUM" 0,05%
- **Process temperature** -40°C...150°C (-40°F...302°F)
- **Pressure measuring range** 100mbar...40bar (1.5psi...600psi)
- **Process pressure absolute / max. overpressure limit** 60bar (900psi)
- **Main wetted parts** Ceraphire ceramic Alloy C 316L Monel PVDF

Phạm vi ứng dụng: The Cerabar PMC71 digital pressure transmitter with capacitive, oil-free ceramic measuring cell is typically used in the process and hygienic applications for pressure, level, volume or mass measurement in liquids and gases. It guarantees high degree of system safety thanks to vacuum-proof ceramic membrane with integrated breakage detection. Quick Setup with adjustable measuring range allows

simple commissioning, reduces costs and saves time. SIL2/3 according to IEC 61508.

Tín năng và thông số kỹ thuật

Continuous / Liquids

Measuring principle

Absolute and gauge pressure

Characteristic / Application

Digital transmitter with capacitive sensor and ceramic membrane

Modular transmitter

Long term stability

Enhanced safety via self diagnostic functions

Secondary process barrier

Specialities

diagnostic functionalities

different languages in software

Supply / Communication

4...20mA HART:

10,5...45V DC

Ex ia: 10,5...30V DC

PROFIBUS PA /

FOUNDATION Fieldbus:

9...32V DC

Accuracy

0,075%

"PLATINUM" 0,05%

Long term stability

0,05% of URL/year

Continuous / Liquids

Ambient temperature

-40°C...85°C
(-40°F...185°F)

Process temperature

-40°C...150°C
(-40°F...302°F)

Process pressure absolute / max. overpressure limit

60bar (900psi)

Pressure measuring range

100mbar...40bar
(1.5psi...600psi)

Main wetted parts

Ceraphire ceramic
Alloy C
316L
Monel
PVDF

Process connection

Threads
Flanges
Tri-Clamp ISO2852
Hygienic connections

Max. measurement distance

400m (1312ft) H2O

Communication

4 ... 20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Continuous / Liquids

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC

Design approvals

EN 10204-3.1

Marine approval

GL/ ABS

Drinking water approvals

NSF

Options

HistoROM/M-Dat

4-line digital display

SS- or Aluminiumhousing

Separate housing

Successor

PMC71B

Application limits

Measuring cell: ceramics

If pressurized, possibly use differential pressure measurement with two pressure transmitters (electronic dp). Observe ratio head pressure : hydrostatic pressure

Pressure

Measuring principle

Absolute and gauge pressure

Pressure

Characteristic

Digital transmitter with capacitive sensor and ceramic membrane

Modular transmitter

Long term stability

Enhanced safety via self diagnostic functions

Secondary process barrier

Supply voltage

4...20 mA HART

10,5...45V DC (Non Ex):

Ex ia: 10,5...30V DC

PROFIBUS PA:

9...32 V DC (Non Ex)

FOUNDATION Fieldbus:

9...32 V DC (Non Ex)

Reference Accuracy

Standard: 0.05%

Platinum: up to 0.025%

Long term stability

0.05 % of URL/ year

0.08 % of URL/ 5 years

0.1 % of URL/ 10 years

Process temperature

-20°C...150°C

(-4°F...257°F)

Pressure

Ambient temperature

-40°C...85°C
(-40°F...185°F)

Measuring cell

100 mbar...40 bar
(1.5 psi...600 psi)

relative/ absolute

Smallest calibratable span

5 mbar (0.075 psi)

Vacuum resistance

0 mbar abs.

Max. Turn down

100:1

Max. overpressure limit

60 bar (900 psi)

Process connection

Thread:

G1/2...G2, R1/2, MNPT1/2...MNPT2

Flange:

DN25...DN80,

ASME 1"...4",

JIS 10K

Pressure

Process connection hygienic

Tri-Clamp

DIN11851

Varivent N

SMS

DRD

Material process membrane

Ceramic

Material gasket

Viton, EPDM, Chemraz, Kalrez, NBR

Fill fluid

none, dry measuring cell

Material housing

Die-cast aluminum,

AISI 316L

Communication

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, EAC

Design approvals

EN10204-3.1

Hygienic approvals

3A, EHEDG

Pressure

Marine approvals

GL/ ABS

Drinking water approvals

NSF

Specialities

Diagnostic functions

Successor

PMC71B

Thông tin bổ sung www.apsc.endress.com/PMC71