

Proline Promass O 300 Coriolis flowmeter

Robust high-pressure flowmeter with a compact, easily accessible transmitter



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/803B

Lợi ích:

- Maximum safety – highest resistance to stress corrosion cracking
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Tổng quan về thông số kỹ thuật

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.35\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 800 000 kg/h (0 to 29 400 lb/min)
- **Medium temperature range** -40 to $+205 \text{ }^\circ\text{C}$ (-40 to $+401 \text{ }^\circ\text{F}$)
- **Max. process pressure** PN 250, Class 1500
- **Wetted materials** Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750) Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Phạm vi ứng dụng: Promass O is designed for premium accuracy of liquids and gases at the highest process pressures in the oil and gas industry. The sensor is fully suitable for offshore conditions and resistant to stress corrosion cracking. With its compact transmitter Promass O 300 offers high flexibility in terms of operation and system integration: access from one side, remote display and improved connectivity options. Heartbeat Technology ensures safe processes.

Tín năng và thông số kỹ thuật

Density/Concentration

Measuring principle

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 150 (3 to 6").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 150 (3 to 6")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Density/Concentration**Max. measurement error**

Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option)

Volume flow (liquid): $\pm 0.10\%$

Mass flow (gas): $\pm 0.35\%$

Density (liquid): $\pm 0.0005\text{ g/cm}^3$

Measuring range

0 to 800 000 kg/h (0 to 29 400 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to $+205\text{ }^\circ\text{C}$ (-40 to $+401\text{ }^\circ\text{F}$)

Ambient temperature range

Standard: -40 to $+60\text{ }^\circ\text{C}$ (-40 to $+140\text{ }^\circ\text{F}$)

Option: -50 to $+60\text{ }^\circ\text{C}$ (-58 to $+140\text{ }^\circ\text{F}$)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Density/Concentration**Outputs**

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communicationHART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safetyFunctional safety according to IEC 61508, applicable in safety-relevant
applications in accordance with IEC 61511

Density/Concentration**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK"

Steam**Measuring principle**

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 150 (3 to 6").

Steam

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 150 (3 to 6")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 800 000 kg/h (0 to 29 400 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Steam**Sensor housing material**

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)
Configuration via local display and operating tools possible
Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Steam

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Liquids

Measuring principle

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Liquids

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 150 (3 to 6").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 150 (3 to 6")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)
Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 800 000 kg/h (0 to 29 400 lb/min)

Max. process pressure

PN 250, Class 1500

Liquids

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Liquids**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK"

Gas**Measuring principle**

Coriolis

Gas

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 150 (3 to 6").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 150 (3 to 6")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Gas

Measuring range

0 to 800 000 kg/h (0 to 29 400 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Gas

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Thông tin bổ sung www.apsc.endress.com/803B