

iTHERM TM402

Imperial Hygienic Thermometer, US style

For standard hygienic and aseptic applications
in the Food & Beverages and Life Sciences
industries



từ **198,98 €**

Giá kể từ 26.09.2022

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TM402

Lợi ích:

- Excellent value for money and fast delivery
- User-friendly and reliable from product selection to maintenance
- International certification: hygiene standards as per 3-A[®], EHEDG, ASME BPE, FDA, TSE Certificate of Suitability
- Wide range of process connections

Tổng quan về thông số kỹ thuật

- **Accuracy** class A acc. to IEC 60751
- **Response time** depending on configuration
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi)
- **Operating temperature range** PT100: -50 °C ... 200 °C (-58 °F ... 392 °F)
- **Max. immersion length on request** up to 15.5" (317,5mm) others on request

Phạm vi ứng dụng: This iTHERM thermometer has been designed to meet the basic requirements of the Food & Beverages and Life Sciences industries at the best price. It offers a variety of versions within a clearly segmented standard product. The result: Time and cost savings by simple and fast product selection. The device uses basic technology with features such as a fixed, non-replaceable insert, a wide range of process connections and international certification at an excellent value for money.

Tín năng và thông số kỹ thuật

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

imperial style
hygienic applications
aseptic applications
hygienic process connections
with neck

Thermowell / protection tube

without (direct immersion)

Insert / probe

without exchangeable insert

Outer diameter protection tube / Insert

1/4" (6,35 mm)
3/8" (9,53 mm)

Max. immersion length on request

up to 15.5" (317,5mm)
others on request

Material protection tube/ thermowell

316L

Process connection

Triclamp
Clamp-connections according to
ISO2852
G3/4" Liquiphant
G1" Liquiphant
Varivent

Tip shape

straight
reduced

Thermometer**Surface roughness Ra**

30 µin (0,76 µm)

15 µin (0,38 µm)

Operating temperature range

PT100:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

Max. process pressure (static)

at 20 °C: 40 bar (580 psi)

Accuracy

class A acc. to IEC 60751

Response time

depending on configuration

Integration head transmitter

yes (4 ... 20 mA, HART)

Certification

SIL (transmitter only)

Thông tin bổ sung www.apsc.endress.com/TM402