

## Radar measurement Micropilot FMR60

The standard sensor for highest demands in liquid level measurement with 80GHz technology



### Lợi ích:

- Hardware and software developed according to IEC 61508 up to SIL3 in homogeneous redundancy
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even with obstructions in vessels due to small beam angle and Multi-Echo Tracking evaluation
- Reduction of engineering effort due to an easier integration of the 80GHz radar instrument into the process
- Innovative drip-off antenna of PTFE for maximum system availability
- The world's easiest proof test concept for SIL and WHG saves time and costs

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FMR60](http://www.apsc.endress.com/FMR60)

### Tổng quan về thông số kỹ thuật

- **Accuracy** +/- 1 mm (0.04 in)
- **Process temperature** -40...+130 °C (-40...+266 °F)
- **Process pressure / max. overpressure limit** Vacuum ...16 bar (Vacuum ... 232 psi)
- **Max. measurement distance** 50 m (164 ft)
- **Main wetted parts** PTFE antenna PP or 316L process connections

**Phạm vi ứng dụng:** Micropilot FMR60 is the first 80GHz radar developed according to the international functional safety directive IEC 61508. The free space radar offers maximum reliability due to the drip-off antenna, improved algorithms and small beam angle. It is used for continuous

non-contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors. It also possesses the smart sensor functionality Heartbeat Technology.

## Tín năng và thông số kỹ thuật

### Continuous / Liquids

#### Measuring principle

Level radar

#### Characteristic / Application

For basic level measurement in liquids, pastes and slurries;  
non affected by changing media, temperature changes, gas blankets or vapor;  
For applications with many obstacles due to the very small beam angle.

#### Specialities

Heartbeat Technology,  
SIL 2/3 according to IEC 61508,  
Bluetooth® commissioning,  
Operation and maintenance SmartBlue App,  
Safety and reliability with Multi-Echo Tracking  
HistoROM  
RFID TAG for easy identification

#### Supply / Communication

2-wire (HART)  
Bluetooth® wireless technology and App (optional)

#### Frequency

W-band (~80 GHz)

#### Accuracy

+/- 1 mm (0.04 in)

#### Ambient temperature

-40...+80 °C  
(-40...+176 °F)

---

**Continuous / Liquids****Process temperature**

-40...+130 °C  
(-40...+266 °F)

---

**Process pressure / max. overpressure limit**

Vacuum ...16 bar  
(Vacuum ... 232 psi)

---

**Main wetted parts**

PTFE antenna  
PP or 316L process connections

---

**Process connection**

Thread:  
G1-1/2", MNPT1-1/2";  
Flange:  
UNI DN80...DN150 (3"...6")

---

**Max. measurement distance**

50 m (164 ft)

---

**Communication**

4...20 mA HART,  
Additional switch,  
Bluetooth® wireless technology

---

**Certificates / Approvals**

ATEX, FM, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC, EAC, UK Ex

---

**Safety approvals**

Overfill protection WHG  
SIL 2, SIL 3

---

**Design approvals**

EN 10204-3.1

---

## Continuous / Liquids

### Options

Display,  
Customized parameterization,  
Remote operation via SmartBlue App using Bluetooth®,  
Gas-tight feed through,  
PWIS free

---

### Application limits

Process temp. > 130 °C (266 °F) -> FMR62  
Very aggressive media -> FMR62  
Strong turbulences and foam, stilling well and bypass -> FMR5x, FMP5x

---

Thông tin bổ sung [www.apsc.endress.com/FMR60](http://www.apsc.endress.com/FMR60)