

iTHERM ModuLine TT131

Welded thermowell for a variety of industrial applications



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/TT131

Lợi ích:

- Modular configuration according to DIN 43772
- iTHERM QuickNeck: cost and time savings thanks to simple, tool-free recalibration of the insert
- Extension, immersion length and total length can be chosen according to process requirements
- Wide choice of dimensions, materials and process connections available
- Specially designed tip for fast response times

Tổng quan về thông số kỹ thuật

- **Max. process pressure (static)** Depending on configuration up to 100 bar
- **Maximum standard immersion length** 4.500 mm (177")
- **Max. immersion length on request** 4.500 mm (177")

Phạm vi ứng dụng: This thermowell designed according to DIN 43772 guarantees a high resistance to most industrial process environments. It is made from pipe or tube and is available in a wide range of diameters and materials. A specially designed thermowell tip ensures fast response times for a more efficient process control. Oversheaths in PTFE or tantalum can withstand extremely corrosive process conditions. It is offered with a variety of process connections: flanges, threads, weld-in or compression fittings.

Tín năng và thông số kỹ thuật

Thermowell

Measuring principle

Fabricated Thermowell

Thermowell

Characteristic / Application

metric style
according to DIN 43772
process connection threaded, flanged, compression
fitting
with neck

Head connection

external thread:
M24 x 1.5, 1/2" NPT, G1/2
Female thread:
M20 x 1.5, 1/2" NPT, G1/2
QuickNeck

Maximum standard immersion length

4.500 mm (177")

Max. immersion length on request

4.500 mm (177")

Thermowell**Process connection**

Thread:

G3/8", G1/2", G3/4", G1"

NPT1/2", NPT3/4", NPT 1"

M18x1.5, M20x1.5, M27x2, M33x2

R1/2", R3/4"

Cap-nut:

M20x1.5, G1/2", G3/4"

Compression fitting:

NPT1/2", G1/2", G1"

Flansche:

DN15 PN40 B1, C

DN25 PN20, PN40, PN100 B1, B2, C

DN40 PN40 B1

DN50 PN40 B1

ASME 1" 150 RF

ASME 1" 300 RF

ASME 1 1/2" 150 RF

ASME 2" 150 RF

ASME 2" 300 RF

Thermowell root diameter

9x1,25 mm

11x2 mm

12x2,5 mm

14x2 mm

16x3,5 mm

1/4" SCH80

1/2" SCH80

1/2" SCH40

Thermowell

Medium contact material

316 (1.4401)
316L (1.4404)
316Ti (1.4571)
Alloy 600 (2.4816)
Alloy C276 (2.4819)
Alloy 446 (1.4749)
Alloy 321 (1.4541)
Sheath PTFE
Sheath Tantal

Wetted part finishing (Ra)

< 1.6 µm (63.00 µin)

Tip shape

straight
reduced
tapered
optimized for quick response times

Temperature range

-200...1.100 °C (-328...2.012 °F)

Max. process pressure (static)

Depending on configuration up to 100 bar

Max. process pressure at 400 °C

Depending on configuration

Thông tin bổ sung www.apsc.endress.com/TT131