

Vibronic

Point level detection

Nivotester FTL325N

Switching unit with NAMUR input for rail mounting or single installation



Lợi ích:

- Nivotester FTL325N for connecting one, two or three measuring cells (1-, 2- or 3-channel devices)
- Intrinsically safe signal circuits Ex ia for use of measuring sensor in explosion hazardous areas
- Functional safety up to SIL2 through line monitoring
- DIN Rail housing for simple series installation on standard rails in switch cabinet
- Simple wiring using pluggable terminal blocks
- NAMUR interface to EN 50227 (DIN 19234; NAMUR) or IEC 60947-5-6 to connect NAMUR sensors or electronic inserts

Phạm vi ứng dụng: Nivotester FTL325N is a switching unit for point level detection in liquid tanks, also in hazardous explosion areas. Also suitable for overfill prevention in tanks with combustible or non-combustible liquids harmful to water. Two-point control and point level detection. The perfect fit for applications in safety related systems with requirements for functional safety up to SIL2 in accordance to IEC 61508 /IEC 61511 using Liquiphant with electronic insert FEL56 or FEL58.

Tín năng và thông số kỹ thuật

Point Level / Liquids

Measuring principle

Vibration Liquids

từ **100,00 €**

Giá kể từ 29.09.2022

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/FTL325N

Point Level / Liquids**Characteristic / Application**

Switching unit NAMUR technology for rail
mounting
SIL2, according 61511
Intrinsically safe

Supply / Communication

NAMUR
24V AC,DC / 230V AC

Ambient temperature

Single installation:
-20 °C ... 60 °C
(-4 °F ... 140 °F)
Rail mounting:
-20 °C ... 50 °C
(-4 °F ... 122 °F)

Communication

1 Channel: 1 level SPDT + 1 alarm SPST
3 Channel: 3 level SPDT + 1 alarm SPST

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO, NEPSI, EAC

Safety approvals

Overfill prevention WHG
SIL

Point Level / Solids**Measuring principle**

Vibration Solids

Characteristic / Application

Switching unit NAMUR technology for rail
mounting
SIL2, according 61511
Intrinsically safe

Point Level / Solids

Supply / Communication

NAMUR

24V AC,DC / 230V AC

Ambient temperature

Single installation:

-20 °C ... 60 °C

(-4 °F ... 140 °F)

Rail mounting:

-20 °C ... 50 °C

(-4 °F ... 122 °F)

Communication

1 Channel: 1 level SPDT + 1 alarm SPST

3 Channel: 3 level SPDT + 1 alarm SPST

Certificates / Approvals

ATEX, FM, CSA, IEC Ex, INMETRO NEPSI

Safety approvals

Overfill prevention WHG

SIL

Thông tin bổ sung www.apsc.endress.com/FTL325N