

Proline Prowirl R 200

Vortex flowmeter

Flowmeter with best-in-class accuracy despite pipe reduction



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/7R2C

Lợi ích:

- Easy energy management – integrated temperature and pressure measurement for steam and gases
- Cost and time savings – no pipework modifications needed for line size reduction
- Same accuracy down to Re 10 000 – most linear Vortex meter body
- Long-term stability – robust drift-free capacitive sensor
- Convenient device wiring – separate connection compartment
- Safe operation – no need to open the device due to display with touch control, background lighting
- Integrated verification – Heartbeat Technology

Tổng quan về thông số kỹ thuật

- **Max. measurement error** Volume flow (liquid): $\pm 0.75\%$ Volume flow (steam, gas): $\pm 1.00\%$ Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated) Mass flow (superheated steam, gas): ± 1.5 (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation) Mass flow (liquid): $\pm 0.85\%$
- **Measuring range** Liquid: 0.1 to 540 m³/h (0.061 to 320 ft³/min) depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68° F) Steam, gas: 0.52 to 7300 m³/h (0.31 to 4300 ft³/min) depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)
- **Medium temperature range** Standard: -40 to +260 °C (-40 to +500 °F) High/low temperature (option): -200 to +400 °C (-328

to +752 °F) High/low temperature (on request): –200 to +450 °C
(–328 to +842 °F)

- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Measuring tube: 1.4408 (CF3M) DSC sensor: 1.4404/F316/F316L Process connection: 1.4404/F316/F316L

Phạm vi ứng dụng: Prowirl R was designed for low flows and is thus the particularly dependable solution for energy management. Additionally its calibration option PremiumCal guarantees excellent measuring accuracy for maximum plant availability. With genuine loop-powered technology, Prowirl R 200 enables cost-effective and seamless integration into existing infrastructures. It offers highest operational safety in hazardous areas. Heartbeat Technology ensures process safety at all times.

Tín năng và thông số kỹ thuật

Liquids

Measuring principle

Vortex

Product headline

Flowmeter with best-in-class accuracy despite pipe reduction.
Easy energy management – integrated temperature and pressure measurement for steam and gases.
Dedicated to applications with very low flow or reduced flow.

Sensor features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10").

Liquids

Transmitter features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10"). Flexible positioning of pressure cell.

Nominal diameter range

DN 25 to 250 (1 to 10")

Wetted materials

Measuring tube: 1.4408 (CF3M)

DSC sensor: 1.4404/F316/F316L

Process connection: 1.4404/F316/F316L

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow difference, temperature

Max. measurement error

Volume flow (liquid): $\pm 0.75\%$

Volume flow (steam, gas): $\pm 1.00\%$

Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated)

Mass flow (superheated steam, gas): $\pm 1.5\%$ (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation)

Mass flow (liquid): $\pm 0.85\%$

Measuring range

Liquid: 0.1 to 540 m³/h (0.061 to 320 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.52 to 7300 m³/h (0.31 to 4300 ft³/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);
air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Max. process pressure

PN 40, Class 300, 20K

Liquids

Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

4 - 20 mA (passive)

Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

Liquids

Power supply

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC

Product safety

CE, C-tick, EAC

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Steam

Measuring principle

Vortex

Product headline

Flowmeter with best-in-class accuracy despite pipe reduction.
Easy energy management – integrated temperature and pressure measurement for steam and gases.
Dedicated to applications with very low flow or reduced flow.

Sensor features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10").

Transmitter features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10"). Flexible positioning of pressure cell.

Nominal diameter range

DN 25 to 250 (1 to 10")

Wetted materials

Measuring tube: 1.4408 (CF3M)

DSC sensor: 1.4404/F316/F316L

Process connection: 1.4404/F316/F316L

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow difference, temperature

Steam

Max. measurement error

Volume flow (liquid): $\pm 0.75\%$

Volume flow (steam, gas): $\pm 1.00\%$

Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated)

Mass flow (superheated steam, gas): $\pm 1.5\%$ (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation)

Mass flow (liquid): $\pm 0.85\%$

Measuring range

Liquid: 0.1 to 540 m³/h (0.061 to 320 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.52 to 7300 m³/h (0.31 to 4300 ft³/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);
air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Max. process pressure

PN 40, Class 300, 20K

Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Steam

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

4 - 20 mA (passive)

Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

Power supply

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC

Product safety

CE, C-tick, EAC

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Steam

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Gas

Measuring principle

Vortex

Product headline

Flowmeter with best-in-class accuracy despite pipe reduction.

Easy energy management – integrated temperature and pressure measurement for steam and gases.

Dedicated to applications with very low flow or reduced flow.

Sensor features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10").

Gas

Transmitter features

Cost and time savings – no pipework modifications needed for line size reduction. Same accuracy down to Re 10 000 – most linear Vortex meter body. Long-term stability – robust drift-free capacitive sensor. Integrated diameter reduction by 1 or 2 line sizes. Nominal diameter (mating pipe) up to DN 250 (10"). Flexible positioning of pressure cell.

Nominal diameter range

DN 25 to 250 (1 to 10")

Wetted materials

Measuring tube: 1.4408 (CF3M)

DSC sensor: 1.4404/F316/F316L

Process connection: 1.4404/F316/F316L

Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow difference, temperature

Max. measurement error

Volume flow (liquid): $\pm 0.75\%$

Volume flow (steam, gas): $\pm 1.00\%$

Mass flow (saturated steam): $\pm 1.7\%$ (temperature compensated); $\pm 1.5\%$ (temperature/pressure compensated)

Mass flow (superheated steam, gas): $\pm 1.5\%$ (temperature/pressure compensated); $\pm 1.7\%$ (temperature compensated + external pressure compensation)

Mass flow (liquid): $\pm 0.85\%$

Measuring range

Liquid: 0.1 to 540 m³/h (0.061 to 320 ft³/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 0.52 to 7300 m³/h (0.31 to 4300 ft³/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a);
air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)

Max. process pressure

PN 40, Class 300, 20K

Gas**Medium temperature range**

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

Inputs

4 - 20 mA (passive)

Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

Gas**Power supply**

DC 12 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4 - 20 mA HART, 4 - 20 mA)

DC 12 to 35 V (4 - 20 mA HART, pulse/frequency/switch output, 4 - 20 mA input)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

Hazardous area approvals

ATEX, IECEx, cCSAus, JPN, EAC

Product safety

CE, C-tick, EAC

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS, LR, BV, DNV GL

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 - 1, similar to ASME IX (on request)

Thông tin bổ sung www.apsc.endress.com/7R2C