

Digital conductivity sensor Condumax CLS15D

Memosens conductive conductivity sensor for standard applications in pure and ultrapure water



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CLS15D

Lợi ích:

- Reliable and accurate measuring values at low conductivities
- Easy to clean thanks to polished measuring surfaces
- Sterilizable and autoclavable
- Quality certificate stating the individual cell constant
- Logging of sensor-specific data for easy traceability and predictive maintenance
- Maximum process safety via non-contact inductive signal transmission
- Convenient maintenance strategy with Memobase Plus for easy data and sensor management

Tổng quan về thông số kỹ thuật

- **Measurement range** $k=0,01$: 0.04 to 20 $\mu\text{S}/\text{cm}$ $k=0,1$: 0.10 to 200 $\mu\text{S}/\text{cm}$
- **Process temperature** Threaded with fixed cable: -20 to 100 °C (-4 to 212 °F) Threaded with plug-in head: -20 to 120 °C (-4 to 248 °F) Sterilization: max. 140 °C (284 °F) for 30 minutes
- **Process pressure** 13 bar at 20 °C (188 psi at 68 °F) 1 bar at 120 °C (14 psi at 248 °F)

Phạm vi ứng dụng: Condumax CLS15D is the digital solution for conductivity measurement in the low measuring ranges. It performs reliably and accurately in a wide range of applications - even in hazardous areas. Designed for low maintenance and a long operating life, the sensor offers best value for money. Condumax CLS15D is not the latest Memosens generation. To get information on the new Memosens CLS15E sensor with extended functionality, click [here](#).

Tín năng và thông số kỹ thuật

Conductivity

Measuring principle

Conductive

Application

Measurement in pure and ultrapure water range, monitoring of ion exchangers, reverse osmosis, distillation, chip cleaning

Characteristic

Analog or digital 2-electrode conductivity sensors

Measurement range

k=0,01: 0.04 to 20 $\mu\text{S}/\text{cm}$

k=0,1: 0.10 to 200 $\mu\text{S}/\text{cm}$

Measuring principle

Conductive conductivity cell with polished stainless steel electrodes

Design

2-electrode conductivity cell with coaxially arranged electrodes, electropolished

Material

Electrode: stainless steel 1.4435

Electrode shaft: PES

Dimension

Electrode diameter: 16 mm (0.63 inch)

Electrode length: appr. 55 mm (2.17 inch)

Process temperature

Threaded with fixed cable:

-20 to 100 °C (-4 to 212 °F)

Threaded with plug-in head:

-20 to 120 °C (-4 to 248 °F)

Sterilization: max. 140 °C (284 °F) for 30 minutes

Conductivity

Process pressure

13 bar at 20 °C (188 psi at 68 °F)

1 bar at 120 °C (14 psi at 248 °F)

Temperature sensor

NTC 30K

Ex certification

ATEX, NEPSI, FM, CSA

Connection

Process: 1/2" and 3/4" NPT, Clamp 1 1/2"

Cable: Memosens connector

Ingres protection

IP68

Additional certifications

Calibration certification of the cell constante, material certification 3.1

Thông tin bổ sung www.apsc.endress.com/CLS15D