

Dosimass Coriolis flowmeter

The compact sensor with an ultra-compact transmitter



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/8BE

Lợi ích:

- High process safety – high measuring accuracy for different media in shortest filling time
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Versatile and time-saving wiring – plug connector
- Fast commissioning – pre-configured devices
- Automatic recovery of data for servicing

Tổng quan về thông số kỹ thuật

- **Max. measurement error** Mass flow (liquid): $\pm 0.15\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 18 000 kg/h (0 to 660 lb/min)
- **Medium temperature range** -40 to $+125 \text{ }^\circ\text{C}$ (-40 to $+257 \text{ }^\circ\text{F}$) $150 \text{ }^\circ\text{C}$ allowed for 1 h
- **Max. process pressure** PN 40
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4404 (316/316L)

Phạm vi ứng dụng: Dosimass is specially designed for filling and bottling applications. It measures volume and mass flow directly with temperature and density compensation to ensure maximum repeatability. Designed for applications where space is a premium, Dosimass will be the preferred choice for system integrators, skid builders and equipment manufacturer.

Tín năng và thông số kỹ thuật

Liquids

Measuring principle

Coriolis

Product headline

The compact sensor with an ultra-compact transmitter.
Measurement of liquids with the most diverse properties in continuous process control & batching applications.

Sensor features

High process safety – high measuring accuracy for different media in shortest filling time. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Nominal diameter: DN 8 to 25 ($\frac{3}{8}$ to 1"). Various hygienic process connections, 3-A conform. CIP, SIP cleanable sensor.

Transmitter features

Versatile and time-saving wiring – plug connector. Fast commissioning – pre-configured devices. Automatic recovery of data for servicing.
Robust, ultra - compact transmitter housing. Pulse/frequency/switch output, Modbus RS485. Excellent and easily cleanable transmitter.

Nominal diameter range

DN 8 to 25 ($\frac{3}{8}$ to 1")

Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow

Max. measurement error

Mass flow (liquid): ± 0.15 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 18 000 kg/h (0 to 660 lb/min)

Liquids

Max. process pressurePN 40

Medium temperature range

-40 to +125 °C (-40 to +257 °F)

150 °C allowed for 1 h

Ambient temperature range-20 to +60 °C (-4 to +140 °F)

Sensor housing material1.4301 (304), corrosion resistant

Transmitter housing material1.4308 (304)

Degree of protectionIP67, type 4X enclosure

Display/Operation

No local operation

Configuration via operating tools possible

OutputsPulse/frequency/switch output (passive)

InputsNone

Digital communicationModbus RS485

Power supplyDC 20 to 30 V

Hazardous area approvalsATEX, IECEx, cCSAus

Liquids

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

3-A

Product safety

CE

Thông tin bổ sung www.apsc.endress.com/8BE