

## Vibronic measurement Density Computer FML621

Measurement of density, reference density, concentration of liquids in conjunction with a Liquiphant



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/FML621](http://www.apsc.endress.com/FML621)

### Lợi ích:

- Measurement used in tanks and pipes without the need for additional pipework
- Large number of process connections to choose from: universal usage
- Integration of existing temperature measurements for temperature compensation
- No mechanically moving parts: no maintenance, no wear, long operating life
- pump dry-run protector can be provided with the same process connection
- Additional calculations, such as the mass of the product, can be performed in the Density Computer FML621
- The integrated data logger supports users during operation and servicing

**Phạm vi ứng dụng:** The density measuring line can be used in all liquid media for medium detection, to calculate the reference density, to calculate the concentration of a liquid, to convert values to different units such as °Brix, °Baumé, °API etc. Additional software modules, such as determining the reference density, intelligent medium differentiation and concentration identification, support the user in monitoring the quality. EEx ia, EEx de and EEx d explosion protection for use in hazardous areas.

### Tín năng và thông số kỹ thuật

## Density

### **Measuring principle**

Vibration Density

---

### **Characteristic / Application**

Density Computer

Software offers modules for density, reference density, concentration of liquids and for a intelligent medium detection

---

### **Supply / Communication**

AC 90-253V

DC 20-36V

---

### **Ambient temperature**

-20...50°C

---

### **Output**

4-20mA

Profibus DP

Ethernet

---

### **Certificates / Approvals**

ATEX

EAC

---

### **Options**

Mathscapabilities for further calculations

---

### **Specialities**

Configuration with ReadWin2000

---

Thông tin bổ sung [www.apsc.endress.com/FML621](http://www.apsc.endress.com/FML621)