

## Digital ORP sensor Memosens CPS42E

Memosens 2.0 ORP sensor for applications with fast-changing medium compositions or low conductivity



Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/CPS42E](http://www.apsc.endress.com/CPS42E)

### Lợi ích:

- Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- Resistant to poisoning due to permanent refilling of KCl bridge electrolyte and separate reference lead
- Perfectly suited for quickly changing media: Combination of liquid KCl electrolyte and ceramic junction enables fast response time
- Applicable at very low conductivities ( $> 5 \mu\text{S}/\text{cm}$ ) thanks to liquid KCl electrolyte
- Suitable for cleaning in place (CIP) and sterilization in place (SIP)
- Maximum process safety through non-contact inductive signal transmission
- Reduced operating costs due to minimized process downtime and extended sensor lifetime

### Tổng quan về thông số kỹ thuật

- **Measurement range**  $-1\ 500$  to  $1\ 500$  mV
- **Process temperature**  $-15$  to  $135$  °C ( $5$  to  $275$  °F)
- **Process pressure**  $0.8$  to  $11$  bar ( $11.6$  to  $159.5$  psi) (absolute)

**Phạm vi ứng dụng:** Memosens CPS42E is the high performer for harsh chemical applications, media with low conductivity or considerable organic content. The sensor is designed for fast response especially in applications with fast-changing media. Thanks to Memosens 2.0 digital technology, CPS42E combines maximum process integrity with simple operation. It resists moisture and enables lab calibration. It offers

extended storage of calibration and process data providing the perfect basis for predictive maintenance.

## Tín năng và thông số kỹ thuật

### ORP / Redox

#### Measuring principle

Sensor ORP / Redox

#### Application

Media with very low conductivity or a high proportion of organic solvents or alcohol:

- Chemical industry
- Organic chemicals
- Power stations
- Laboratory measurements

#### Characteristic

Digital ORP electrode for process engineering with ceramic junction and KCl liquid electrolyte

#### Measurement range

-1 500 to 1 500 mV

#### Measuring principle

Liquid-KCl filling and ceramic junction

#### Design

All shaft lengths with temperature sensor

## ORP / Redox

**Material**

Sensor shaft: Glass to suit process

ORP measuring element: Platinum

Metal lead: Ag/AgCl

Open aperture: Ceramic junction, zirconium dioxide

O-ring: FKM

Process coupling: PPS fiber-glass reinforced

Nameplate: Ceramic metal oxide

---

**Dimension**

Diameter: 12 mm (0.47 inch)

Shaft length: 120, 225, 360 and 425 mm  
(4.72, 8.86, 14.17 and 16.73 inch)

---

**Process temperature**

-15 to 135 °C (5 to 275 °F)

---

**Process pressure**

0.8 to 11 bar (11.6 to 159.5 psi) (absolute)

---

**Temperature sensor**

NTC 30k

---

**Ex certification**

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals for use in hazardous areas Zone 0, Zone 1 and Zone 2.

---

**Connection**

Inductive, contactless connection head with Memosens 2.0 technology

---

ORP / Redox

**Ingres protection**

IP68

---

**Additional certifications**

Additional certifications

---

Thông tin bổ sung [www.apsc.endress.com/CPS42E](http://www.apsc.endress.com/CPS42E)