

Deltatop DP62D



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/DP62D

Lợi ích:

- Selectable according to the application: operational compact version or modular remote version
- Optimized for minimum pressure loss and highest accuracy
- Deltabar differential pressure transmitter ready adjusted
- Display configured for flow rate, differential pressure or 0 to 100 %
- Suited for bidirectional measurements
- Cost-effective solution thanks to its robust design without moving parts

Tổng quan về thông số kỹ thuật

- **Max. measurement error** typically 1% of calculated volume or mass. Uncertainty of primary element excluding uncertainty of density or compensation.
- **Measuring range** 200 ... 500'000m³/h
- **Medium temperature range** Compact version: -200°C ... 200°C -328°F ... 392°F Remote version: -200°C ... 1000°C -328°F ... 1832°F
- **Max. process pressure** PN6 ... 250 Cl.300 ... 1500

Phạm vi ứng dụng: The Deltatop DP62D is part of the differential pressure flow measurement with orifices and Deltabar differential pressure transmitter. It is an average pressure Pitot tube with diamond profile, which has the possibility to have an integrated temperature measurement.

Tín năng và thông số kỹ thuật

Gas

Measuring principle

Differential pressure

Gas

Product headline

Calculated volume or mass flow measurement. dp primary element (Pitot).

Averaging pitot tube with 25,4mm diamond profile.

Sensor features

Insertion system.

Pipe size DN100...2000 ; 4...80".

Retractable version available.

Bidirectional measurement.

Compact or remote design.

Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 100...2000

4" ... 80"

Max. measurement error

typically 1% of calculated volume or mass.

Uncertainty of primary element excluding uncertainty of density or compensation.

Measuring range

200 ... 500'000m³/h

Max. process pressure

PN6 ... 250

Cl.300 ... 1500

Medium temperature range

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Gas**Degree of protection**

Transmitter (Deltabar):
IP67
NEMA6P

Display/Operation

Transmitter (Deltabar):
4-line display
3 push buttons
Quick setup
HistoROM

Outputs

Transmitter (Deltabar):
4 ... 20 mA

Digital communication

Transmitter (Deltabar):
HART
PROFIBUS PA
FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):
ATEX
FM
CSA
IEC
TIIS
NEPSI

Liquids**Measuring principle**

Differential pressure

Liquids

Product headline

Calculated volume or mass flow measurement. dp primary element (Pitot).

Averaging pitot tube with 25,4mm diamond profile.

Sensor features

Insertion system.

Pipe size DN100...2000 ; 4...80".

Retractable version available.

Bidirectional measurement.

Compact or remote design.

Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 100...2000

4" ... 80"

Max. measurement error

typically 1% of calculated volume or mass.

Measuring range

8.0 ... 17'500m³/h

Max. process pressure

PN6 ... 250

Cl.300 ... 1500

Medium temperature range

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Liquids**Degree of protection**

Transmitter (Deltabar):
IP67
NEMA6P

Display/Operation

Transmitter (Deltabar):
4-line display
3 push buttons
Quick setup
HistoROM

Outputs

Transmitter (Deltabar):
4 ... 20 mA

Digital communication

Transmitter (Deltabar):
HART
PROFIBUS PA
FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):
ATEX
FM
CSA
IEC
TIIS
NEPSI

Steam**Measuring principle**

Differential pressure

Steam

Product headline

Calculated volume or mass flow measurement. dp primary element (Pitot).

Averaging pitot tube with 25,4mm diamond profile.

Sensor features

Insertion system.

Pipe size DN100...2000 ; 4...80".

Retractable version available.

Bidirectional measurement.

Compact or remote design.

Deltabar S/M differential pressure transmitter.

Nominal diameter range

DN 100...2000

4" ... 80"

Max. measurement error

typically 1% of calculated volume or mass.

Uncertainty of primary element excluding uncertainty of density or compensation.

Measuring range

200 ... 200'000 m³/h

1'000 ... 1'000'000 kg/h at 10bar/230°C

Max. process pressure

PN6 ... 250

Cl.300 ... 1500

Medium temperature range

Compact version:

-200°C ... 200°C

-328°F ... 392°F

Remote version:

-200°C ... 1000°C

-328°F ... 1832°F

Steam

Degree of protection

Transmitter (Deltabar):

IP67

NEMA6P

Display/Operation

Transmitter (Deltabar):

4-line display

3 push buttons

Quick setup

HistoROM

Outputs

Transmitter (Deltabar):

4 ... 20 mA

Digital communication

Transmitter (Deltabar):

HART

PROFIBUS PA

FOUNDATION Fieldbus

Hazardous area approvals

Transmitter (Deltabar):

ATEX

FM

CSA

IEC

TIIS

NEPSI

Thông tin bổ sung www.apsc.endress.com/DP62D