

Gauge pressure Cerabar PMC11

Cost-effective pressure transducer with ceramic sensor for measurement in gases or liquids



từ **146,00 €**

Giá kể từ 12.05.2021

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/PMC11

Lợi ích:

- Easy and time-saving installation and set up within the plant due to very compact construction and customizable measuring ranges
- Reference accuracy of 0.5% together with high long-term stability and repeatability ensures a high quality of process monitoring in standard processes
- Capacitive oil-free measuring cell with high abrasion resistance and 100% test coverage during production guarantees long process availability

Tổng quan về thông số kỹ thuật

- **Accuracy** 0.5%
- **Process temperature** -25 °C...+85 °C (-13 °F...+185 °F)
- **Pressure measuring range** +400 mbar...+40 bar (+6 psi...+600 psi)
- **Measuring cell** +400 mbar...+40 bar (+6 psi...+600 psi)

Phạm vi ứng dụng: The Cerabar PMC11 is the most price-attractive compact pressure transmitter in its segment. It features a capacitive, oil-free ceramic sensor and is able to measure gauge pressure from 400mbar up to 40bar. The PMC11 is designed for standard applications in the process industry and to withstand the conditions with the use of high quality materials like 316L and 99,9% Al₂O₃.

Tín năng và thông số kỹ thuật

Pressure**Measuring principle**Gauge pressure

CharacteristicCost effective pressure transducer, capacitive sensor with ceramics measuring diaphragm

Supply voltage

Analogue output: 10...30 VDC

0...10 V output: 12...30 VDC

Reference Accuracy0.5 %

Long term stability0.2 % of URL/year

Process temperature

-25 °C...+85 °C

(-13 °F...+185 °F)

Ambient temperature

-40 °C...+70 °C

(-40 °F...+158 °F)

Measuring cell

+400 mbar...+40 bar

(+6 psi...+600 psi)

Max. overpressure limitmax. 60 bar (900 psi)

Pressure**Process connection**

Threads:

G1/4, G1/2,

MNPT 1/4, MNPT 1/2,

DIN13

Communication

4...20 mA

0...10 V

Design approvals

EN10204-3.1 Final inspection report

Cleaned from oil and grease

Continuous / Liquids**Measuring principle**

Gauge pressure

Characteristic / Application

Cost effective pressure transducer, capacitive sensor with ceramics measuring diaphragm

Supply / Communication

Analogue output:

10...30 VDC

0...10 V output:

12...30 VDC

Continuous / Liquids**Accuracy**

0.5%

Long term stability

0.2 % of URL/year

Ambient temperature

-40 °C...+70 °C

(-40 °F...+158 °F)

Process temperature

-25 °C...+85 °C

(-13 °F...+185 °F)

Process pressure absolute / max. overpressure limit

max. 60 bar (900 psi)

Pressure measuring range

+400 mbar...+40 bar

(+6 psi...+600 psi)

Process connection

Threads:

G1/4, G1/2,

MNPT 1/4, MNPT 1/2,

DIN13

Communication

4...20 mA

0...10 V

Continuous / Liquids

Design approvals

EN10204-3.1 Final inspection report

Cleaned from oil and grease

Thông tin bổ sung www.apsc.endress.com/PMC11