

Flow assembly Flowfit CYA21

Universal assembly for analytical measuring points in power plants and industrial utilities.



Lợi ích:

- Easy realization of measuring points for quality monitoring of process media like boiler feed water or condensate.
- Robust stainless steel assembly for use under demanding process conditions (maximum 16 bar at 100°C).
- Open pipe outlets for easy integration into common compression fitting systems.
- Easy installation thanks to the enclosed installation kit.

Tổng quan về thông số kỹ thuật

- **Process pressure** Max. 16 bar (relative)

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CYA21

Phạm vi ứng dụng: The Flowfit CYA21 flow assembly is suitable for installation in analytical measuring points in power plants and industrial utilities. Thanks to its design in high-quality stainless steel, it can also be used continuously in applications with high process pressures of up to 16 bar at 100°C. The assembly is very easy to install because it fits into all common compression fitting systems. It can be used to create measuring points for pH/ORP, conductivity or dissolved oxygen.

Tín năng và thông số kỹ thuật

pH

Measuring principle

Potentiometric

Application

Quality control of pure water, condensate, permeate

pH	Installation Fixed installation assembly
	Characteristic Bypass
	Design Flow through assembly
	Material Stainless steel
	Process pressure Max. 16 bar (relative)
	Connection Open pipe endings (outer diameter 6 mm)

ORP / Redox	Measuring principle Conductive
-------------	--

Oxygen	Measuring principle Conductive
--------	--

Conductivity	Measuring principle Potentiometric
--------------	--

Thông tin bổ sung www.apsc.endress.com/CYA21