

T14

Explosion proof Pt100 thermometer, US style

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/T14

Lợi ích:

- FM/CSA XP Class I, Div. 1 approved temperature assemblies for maximum safety
- One source shopping for temperature measurement solutions. World class transmitter with integrated sensor offering for heavy process industry applications
- Remove and install straight out of the box!
- Improved galvanic isolation on most devices (2 kV)
- Simplified model structure: Competitively priced, offers great value. Easy to order and reorder. A single model number includes sensor, thermowell and transmitter assembly for a complete point solution
- All iTEMP transmitters provide long term stability $\leq 0.05\%$ per year

Tổng quan về thông số kỹ thuật

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Response time** depending on configuration 63% $r_t = 20$ s
- **Max. process pressure (static)** at 20 °C: 500 bar (7.252 psi) depends on configuration
- **Operating temperature range** PT100 WW: -200 °C ... 600 °C (-328 °F ... 1.112 °F) PT100 TF: -50 °C ... 200 °C (-58 °F ... 392 °F)
- **Max. immersion length on request** up to 22.5" (571 mm) others on request

Phạm vi ứng dụng: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust thermowells and

special materials. A optional head transmitter with all common communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. Flexible configuration possible.

Tín năng và thông số kỹ thuật

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

Explosion Proof US style

modular temperature assembly

for heavy duty applications

flanged process connection

with extension

incl. thermowell

Thermowell / protection tube

bar stock (drilled)

Insert / probe

mineral insulated (MI), flexible

PTFE-insulated, rigid

Outer diameter protection tube / Insert

7/8" (22,23 mm)

17/16" (26,99 mm)

Thermometer

Max. immersion length on request

up to 22.5" (571 mm)

others on request

Material protection tube/ thermowell

316/316L

others on request

Optional coating

Available on request

Thermometer**Process connection**

flange:

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

ASME 1" 600 RF (B16.5)

ASME 1" 900/1500 RF (B16.5)

ASME 1,5" 150 RF (B16.5)

ASME 1,5" 300 RF (B16.5)

ASME 1,5" 600 RF (B16.5)

ASME 1,5" 900/1500 RF (B16.5)

ASME 2" 150 RF (B16.5)

ASME 2" 300 RF (B16.5)

ASME 2" 600 RF (B16.5)

ASME 2" 900/1500 RF (B16.5)

Tip shape

straight

tapered

Surface roughness Ra

32 µin. (0.80 µm)

Thermometer**Operating temperature range**

PT100 WW:

-200 °C ... 600 °C

(-328 °F ... 1.112 °F)

PT100 TF:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

Max. process pressure (static)

at 20 °C: 500 bar (7.252 psi)

depends on configuration

Accuracy

class A acc. to IEC 60751

class B acc. to IEC 60751

Response time

depending on configuration

63% rt = 20 s

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Thermometer

Ex - approvals

FM XP

CSA XP

FM/CSA XP

CSA GP

Certification

SIL (transmitter only)

Thông tin bổ sung www.apsc.endress.com/T14