

T15

Explosion proof RTD thermometer, US style

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/T15

Lợi ích:

- FM/CSA XP Class I, Div. 1 approved temperature assemblies for maximum safety
- One source shopping for temperature measurement solutions. World class transmitter with integrated sensor offering for heavy process industry applications
- Remove and install straight out of the box!
- Improved galvanic isolation on most devices (2 kV)
- Simplified model structure: Competitively priced, offers great value. Easy to order and reorder. A single model number includes sensor, thermowell and transmitter assembly for a complete point solution
- All iTEMP transmitters provide long term stability $\leq 0.05\%$ per year

Tổng quan về thông số kỹ thuật

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Response time** 63% $t_r = 3$ s
- **Max. process pressure (static)** Not applicable
- **Operating temperature range** PT100 WW: -200 °C ... 600 °C (-328 °F ... 1.112 °F) PT100 TF: -50 °C ... 200 °C (-58 °F ... 392 °F)
- **Max. immersion length on request** up to 100" (2540 mm) others on request

Phạm vi ứng dụng: The robust device is a unit ready for use within and existing thermowell and includes various housing transmitter heads to meet the application and space requirement needs. The unit offers enhanced measurement accuracy and reliability. A variety of connections,

dimensions and materials (like 316L SS and Hastelloy C276) offer flexible application possibilities.

Tín năng và thông số kỹ thuật

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

Explosion Proof US style

modular temperature assembly

for heavy duty applications

with extension

to be used with existing thermowell

Thermowell / protection tube

to be used with thermowell

Insert / probe

mineral insulated (MI), flexible

PTFE-insulated, rigid

Outer diameter protection tube / Insert

Not applicable

Max. immersion length on request

up to 100" (2540 mm)

others on request

Thermometer

Material protection tube/ thermowell

Sensor sheath

316/316L

Optional coating

Not defined

Process connection

male thread:

NPT1/2"

Tip shape

straight

Surface roughness Ra

Not defined

Operating temperature range

PT100 WW:

-200 °C ... 600 °C

(-328 °F ... 1.112 °F)

PT100 TF:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

Max. process pressure (static)

Not applicable

Thermometer**Accuracy**

class A acc. to IEC 60751

class B acc. to IEC 60751

Response time63% rt = 3 s

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

FM XP

CSA XP

FM/CSA XP

CSA GP

CertificationSIL (transmitter only)

Thông tin bổ sung www.apsc.endress.com/T15