

RID14

8 channel field indicator for fieldbuses

Indication of up to 8 process or calculated values for FOUNDATION Fieldbus™ or PROFIBUS® PA protocol



từ **521,00 €**

Giá kể từ 23.04.2021

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/RID14

Lợi ích:

- Simple and standardized communication via fieldbus protocol
- Listener mode for up to 8 input channels or digital status
- Brilliant, backlit LC display with bar graph, diagnostic symbols and clear text field
- No external power supply required
- International approvals

Tổng quan về thông số kỹ thuật

- **Input** Foundation Fieldbus protocol PROFIBUS PA protocol
- **Output** Not defined
- **Display** High contrast backlit LCD with bargraph TAG/unit
- **Power Supply** Not defined

Phạm vi ứng dụng: The 8 channel indicator shows measured and calculated values and status information of the fieldbus users in a FOUNDATION Fieldbus™ or PROFIBUS® PA network. In the listener mode the device listens to the set fieldbus addresses and indicates their values. In addition, for FOUNDATION Fieldbus™ values available on the bus can be indicated via function block interconnection. A plain text field allows the display of the engineering unit or of the TAG. A bar graph is available for trend visualization.

Tín năng và thông số kỹ thuật

Acquisition / Evaluation**Measuring principle**Display

Function

Display values

Advanced diagnostic

Certification

ATEX Ex ia

ATEX Ex d

FM

CSA

IECEX Ex ia

IECEX Ex d

IECEX Ex tD

Input

Foundation Fieldbus protocol

PROFIBUS PA protocol

Dimensions (wxhxd)

Field housing:

132 x 135 x 106 mm

(5.2" x 5.31" x 4.17")

Acquisition / Evaluation**Software**

Listener Mode

On Foundation Fieldbus also function block connection:

Display transducer block

Advanced diagnostic block´

2 x input selector

Arithmetic block

Integrator block

PID block

Operation

Foundation Fieldbus: via fieldbus

PROFIBUS PA: DTM and FieldCare or DIP-switches on the device

Write lock on hardware

Display

High contrast backlit LCD with bargraph

TAG/unit

Operating Voltage

9-32 V DC, polarity independent

Process indicator & control
units

Measuring principle
Fieldbus indicators

Measuring principle
8 channel field indicator for fieldbuses

Function
Display values

Advanced diagnostic

Display
High contrast backlit LCD with bargraph

TAG/unit

Power Supply
Not defined

Input
Foundation Fieldbus protocol

PROFIBUS PA protocol

Output
Not defined

Output
Not defined

Process indicator & control units**Software functions**

Listener Mode

On Foundation Fieldbus also function block connection:

Display transducer block

Advanced diagnostic block

2 x input selector

Arithmetic block

Integrator block

PID block

Certificates

ATEX Ex ia

ATEX Ex d

FM

CSA

IECEX Ex ia

IECEX Ex d

IECEX Ex tD

SILNot defined

Process indicator & control
units

Panel mounting
field

Thông tin bổ sung www.apsc.endress.com/RID14