

Guided radar measurement Time-of-Flight Levelflex FMP50

For all basic level applications in liquids



Lợi ích:

- Reliable measurement even for changing product and process conditions
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability due to new Multi-Echo Tracking evaluation
- Hardware and software developed according to IEC 61508 up to SIL3
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test for SIL and WHG saves time and costs

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/FMP50

Tổng quan về thông số kỹ thuật

- **Accuracy** Rod probe: +/- 2 mm (0.08 in) Rope probe: +/- 2 mm (0.08 in)
- **Process temperature** -20...+80 °C (-4...+176 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum...6 bar, (Vacuum...87 psi)
- **Max. measurement distance** Rod: 4 m (13 ft) Min DK>1.6 Rope: 12 m (40 ft) Min DK>1.6
- **Main wetted parts** Rod probe: 316L, PPS, Viton Rope probe: 316, PPS, Viton

Phạm vi ứng dụng: Levelflex FMP50 is the instrument for basic applications in liquids which do not place high demands on temperature and pressure ranges or chemical resistance. Particularly in basic supply or storage applications as well as utility processes FMP50 is the best choice.

Levelflex FMP50 guided radar is used for continuous level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors.

Tín năng và thông số kỹ thuật

Continuous / Liquids

Measuring principle

Guided radar

Characteristic / Application

Basic device

Rod probe, Rope probe

Integrated data memory, Factory precalibrated, Reliable measuring for changing medias.

Specialities

Heartbeat Technology,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

HistoROM,

RFID TAG for easy identification

Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

Accuracy

Rod probe: +/- 2 mm (0.08 in)

Rope probe: +/- 2 mm (0.08 in)

Ambient temperature

-20...+80 °C

(-4...+176 °F)

Process temperature

-20...+80 °C

(-4...+176 °F)

Continuous / Liquids**Process pressure absolute / max. overpressure limit**

Vacuum...6 bar,
(Vacuum...87 psi)

Main wetted parts

Rod probe: 316L, PPS, Viton
Rope probe: 316, PPS, Viton

Process connection

Thread:
G 3/4, MNPT 3/4
Flange:
UNI Flange

Sensor length

Rod probe: 4 m (13 ft)
Rope probe: 12 m (40 ft)

Max. measurement distance

Rod: 4 m (13 ft) Min DK>1.6
Rope: 12 m (40 ft) Min DK>1.6

Communication

4...20 mA HART
PROFIBUS PA
FOUNDATION Fieldbus
Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, INMETRO, NEPSI, KC, EAC, UK Ex

Safety approvals

Overfill protection WHG
SIL

Design approvals

EN 10204-3.1

Continuous / Liquids

Options

Sensor remote with 3 m/ 9 ft cable,
Remote operation via SmartBlue App using Bluetooth®

Application limits

Application limits

Thông tin bổ sung www.apsc.endress.com/FMP50