

Immersion assembly Dipfit CPA111

Universal assembly for the water and wastewater industry



Lợi ích:

- Simple installation and removal of electrode holder due to bayonet lock
- Flexible immersion depth thanks to adjustable flange
- Reduces installation effort by providing 3 mounting positions for 120 mm sensors or an optional cleaning unit
- Made of environmentally compatible polypropylene material

Tổng quan về thông số kỹ thuật

- **Process temperature** Max. 80 °C (176 °F)
- **Process pressure** Max. 4 bar at 20°C (Max. 58 psi at 68°F)

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CPA111

Phạm vi ứng dụng: The Dipfit CPA111 immersion assembly is designed for applications in open and closed tanks. It offers space for three sensors that can be easily mounted and removed via the bayonet lock. The adjustable flange gives you the required flexibility for universal use. Dipfit is the time- and cost-efficient solution for standard water and wastewater treatment.

Tín năng và thông số kỹ thuật

pH

Measuring principle

Potentiometric

Application

Water, waste water, process

pH

Installation

Immersion assembly

Characteristic

For open and closed tanks and channels

Design

Bayonet technology, 3 electrode installation locations,
120 mm electrodes, variable holder length, integrated spray cleaning
CPR31, external spray cleaning CPR30, process connection with fix or
adjustable flange

Material

Sensor holder: PP-GF 20

Immersion tube: PP

Dimension

Length: 500 to 3000 mm (19.7 to 118 inch), special lengths on request

Process temperature

Max. 80 °C (176 °F)

Process pressure

Max. 4 bar at 20°C

(Max. 58 psi at 68°F)

Connection

Suspended assembly, lap joint flange DN100

Pressurized flange DN100/PN4, adjustable flange DN100

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Water, waste water, process

ORP / Redox

Installation

Immersion assembly

Characteristic

For open and closed tanks and channels

Design

Bayonet technology, 3 electrode installation locations, 120 mm electrodes, variable assembly length, integrated spray cleaning CPR31, external spray cleaning CPR30, process connection with fix or adjustable flange

Material

Sensor holder: PP-GF 20

Immersion tube: PP

O-ring: VITON

Dimension

500 to 3000 mm (19.7 to 118 inch), special lengths on request

Process temperature

max. 80°C

(176°F)

Process pressure

max. 4 bar at 20°C

(58 psi at 68°F)

Connection

- Suspended assembly - lap joint flange DN100- pressurized flange DN100/PN4 - adjustable flange DN100

Thông tin bổ sung www.apsc.endress.com/CPA111