

## RIA452

### Process indicator with pump control

Digital process meter in panel mounted housing for monitoring and displaying analog measured values



từ **385,00 €**

Giá kể từ 02.12.2021

Thông tin thêm và mức tính giá hiện tại:

[www.apsc.endress.com/RIA452](http://www.apsc.endress.com/RIA452)

#### Lợi ích:

- 7-digit 14-segment LC display, large bar graph with overrange and underrange
- Digital status inputs for pump monitoring
- Flow measurement for open channels and weirs
- Intrinsically safe input with integrated loop power supply
- Min/Max value saved
- Linearization table with up to 32 support points

#### Tổng quan về thông số kỹ thuật

- **Input** 1 x analog (U, I, RTD, TC, R)
- **Output** 1 x analog (U, I) 1 x transmitter power supply
- **Output** 1 x analog (U, I) 1 x transmitter power supply
- **Display** LCD multicolour Illuminated Bargraph
- **Power Supply** 90...250 V AC 20...28 V AC 20...36 V DC

**Phạm vi ứng dụng:** The process meter monitors and displays the analog measured values. Pumps can be monitored with the digital status inputs. The RIA452 can provide power directly to two-wire sensors connected. Up to eight freely programmable relays monitor the measured value. Other operating modes for the relays include sensor or device malfunction, batch and pump control functions. Furthermore, the RIA452 can be used as a preset counter and for measuring flow at open channels and measuring weirs.

#### Tín năng và thông số kỹ thuật

---

**Acquisition / Evaluation****Measuring principle**Display

---

**Function**

Display

Power

Switch

Seperate

Convert

Count

Calculate

---

**Certification**

UL rec. Comp

ATEX Ex i

FM USA IS

FM USA NI

CSA IS

CSA NI

TIIS Ex ia

---

**Input**1 x analog (U, I, RTD, TC, R)

---

**Output**

1 x analog (U, I)

1 x transmitter power supply

---

**Relay output**4...8 x changeover contacts

---

**Auxiliary power supply / Loop power supply**

90...250 V AC

20...28 V AC

20...36 V DC

---

---

**Acquisition / Evaluation****Dimensions (wxhxd)**

Panel housing:  
96 x 96 x 161.3 mm  
(3.78" x 3.78" x 6.35")

---

**Software**

Pump control  
Linearisation  
Flow calculation  
Batch counter

---

**Operation**

3 keys  
Interface RS252 + ReadWin2000

---

**Display**

LCD multicolour  
Illuminated  
Bargraph

---

**Process indicator & control units****Measuring principle**

Indicators with control unit

---

**Measuring principle**

Process indicator with pump control

---

**Function**

Display  
Power  
Switch  
Seperate  
Convert  
Count  
Calculate

---

---

**Process indicator & control units****Display**

LCD multicolour  
Illuminated  
Bargraph

---

**Power Supply**

90...250 V AC  
20...28 V AC  
20...36 V DC

---

**Input**

1 x analog (U, I, RTD, TC, R)

---

**Output**

1 x analog (U, I)  
1 x transmitter power supply

---

**Output**

1 x analog (U, I)  
1 x transmitter power supply

---

**Software functions**

Pump control  
Linearisation  
Flow calculation  
Batch counter

---

**Certificates**

Non-hazardous area  
FM  
CSA  
W/o ATEX approval, Ex-sensor supply via external  
RB223

---

**SIL**

Not defined

---

**Panel mounting**

panel mounting

---

Process indicator & control  
units

Thông tin bổ sung [www.apsc.endress.com/RIA452](http://www.apsc.endress.com/RIA452)