

Suspended solids sensor Turbimax CUS51D

Memosens sensor for suspended solids and turbidity measurement in water, wastewater and utilities



Lợi ích:

- One sensor for all applications: The 'one for all' principle optimizes stockholding, speeds up project handling and simplifies life cycle management.
- Optimum adaption to all measuring tasks: Sensor fits all measuring ranges thanks to numerous integrated analytical models.
- Fast and easy commissioning: Sensor comes precalibrated and preconfigured ex factory.
- Enables unattended plant operation: Intelligent design enables sophisticated self-cleaning capabilities and minimizes maintenance.
- Perfect process adaption: Fast sensor positioning with holder and assembly system Flexdip CYA112 and CYH112.

Thông tin thêm và mức tính giá hiện tại:

www.apsc.endress.com/CUS51D

Tổng quan về thông số kỹ thuật

- **Measurement range** For formazin: 0 to 4000 FNU Display range up to 9999 FNU For sludge: 0 to 300 g/L The achievable measuring range depends very much on the media
- **Process temperature** Process temperature: -5 to 50 °C (23 to 122 °F) Ambient temperature: -20 to 60 °C (-4 to 140 °F)

Phạm vi ứng dụng: Turbimax CUS51D is a smart sensor that allows unattended operation in a wide range of process conditions. Its unique design is extremely robust and it is also low-maintenance thanks to its self-cleaning functionality. Choose from different integrated analytical models to adapt the sensor to your specific application. With Memosens digital technology, the CUS51D combines maximum process and data

integrity with simple operation. It resists corrosion and moisture and enables lab calibration.

Tín năng và thông số kỹ thuật

Turbidity

Measuring principle

Four beam alternating light

Application

Wastewater, process water and primary water treatment applications.

Turbidity and suspended solids measurement at all stages of the wastewater treatment process and at primary water treatment applications with medium to high turbidities.

Installation

Insitu (immersion in process or retractable holder), extractive with sample and flow cell

Measurement range

For formazin: 0 to 4000 FNU

Display range up to 9999 FNU

For sludge: 0 to 300 g/L

The achievable measuring range depends very much on the media

Measuring principle

Scattered light in 90°/135° and 4beam cross light

Design

40 mm sensor, stainless steel

Material

Stainless steel 316L

Dimension

194 mm x 40 mm

Turbidity

Process temperature

Process temperature:
-5 to 50 °C (23 to 122 °F)

Ambient temperature:
-20 to 60 °C (-4 to 140 °F)

Connection

G1, NPT3/4"

Ingress protection

IP68 (1 m / 3.3 ft) water column with 1N KCl during 60 days

Thông tin bổ sung www.apsc.endress.com/CUS51D