

Proline Promag W 800

Electromagnetic flowmeter

Long-lasting battery-powered magmeter with secure system integration and communication



Benefits:

- With corrosion protection for underground installation or permanent underwater use
- Improved process safety – leakage detection with low flow and pressure measurement
- Reliable measurement – accurate measured values even with 0 x DN inlet run
- Long-term operation – robust and completely welded sensor
- Secure data storage and transmission – worldwide encrypted communication over the mobile network
- Convenient commissioning and operation – device access via Bluetooth using intuitive SmartBlue app
- Integrated verification – Heartbeat Technology

More information and current pricing:

www.at.endress.com/5W8C

Specs at a glance

- **Max. measurement error** Volume flow: $\pm 0.5\%$ o.r. ± 2 mm/s ($\pm 0.5\%$ o.r. ± 0.08 in/s)
- **Measuring range** 15 dm³/min to 2500 m³/h (4 to 11 000 gal/min)
- **Medium temperature range** Liner material hard rubber: 0 to +80 °C (+32 to +176 °F) Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Liner: polyurethane; hard rubber Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022)

Field of application: Promag W 800 is ideal for off-grid applications in the water industry, even flow measurement in direct underground installation or underwater. Promag 800 covers basic functionality,

Promag 800 Advanced offers the full performance spectrum. The battery-powered transmitter provides worldwide transmission of measured data without additional energy supply. Heartbeat Technology ensures measurement reliability and compliant verification.

Features and specifications

Liquids

Measuring principle

Electromagnetic

Product headline

Battery-powered flowmeter with EN ISO 12944 corrosion protection & intelligent energy efficient mode.

For direct underground installation or permanent underwater use. Certified sensor for the most demanding water and wastewater applications.

Sensor features

Secure, reliable long - term operation – robust and completely welded sensor. Energy - saving flow measurement – no pressure loss due to cross section constriction. Maintenance - free – no moving parts. International drinking water approvals. Degree of protection IP68 (Type 6P enclosure). Transmitter housing made of durable polycarbonate.

Transmitter features

No power grid required – battery lifetime of up to 15 years. Worldwide transmission of measured data and events via e-mail and SMS – integrated GSM/GPRS modem. Reliable data storage – integrated SD card.

All in 1 housing incl. batteries & wireless modem. Measuring intervals can be adapted individually.

Nominal diameter range

DN 25 to 600 (1 to 24")

Wetted materials

Liner: polyurethane; hard rubber

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022)

Liquids

Measured variables

Volume flow

Max. measurement error

Volume flow: $\pm 0.5\%$ o.r. ± 2 mm/s ($\pm 0.5\%$ o.r. ± 0.08 in/s)

Measuring range

15 dm³/min to 2500 m³/h (4 to 11 000 gal/min)

Max. process pressure

PN 40, Class 300, 20K

Medium temperature range

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Ambient temperature range

Flange material carbon steel: -10 to +60 °C (14 to +140 °F)

Flange material stainless steel: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

Standard: Carbon steel with protective varnish, fully welded

Sensor connection housing: Polycarbonate

Transmitter housing material

Polycarbonat

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP68, type 6P enclosure, with protective varnish according to EN ISO 12944 C5 - M/Im1/Im2/Im3.

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible; Remote data access via mail and SMS

Liquids

Outputs

Pulse/switch output (passive)

Inputs

Status input

Digital communication

GSM/GPRS

Power supply

Internal:

Batteries per DC 3.6 V External:

AC 100 to 240 V (44 to 66 Hz) / DC 12 to 60 V

Hazardous area approvals

None

Metrological approvals and certificates

3.1 material, calibration performed on accredited calibration facilities
(acc. to ISO/IEC 17025)

Pressure approvals and certificates

CRN

Hygienic approvals and certificates

Drinking water approval: ACS, KTW/W270, NSF 61, WRAS BS 6920

More information www.at.endress.com/5W8C