


TSC310

Thermocouple sensor, cable probe

Cost efficient thermocouple sensor designed for use in many process and laboratory applications



More information and current pricing:

www.at.endress.com/TSC310

Benefits:

- High flexibility through user-specific insertion lengths and variable process connections
- Fast response time
- Different types of thermocouples according to DIN EN 60584 and ASTM E230/ANSI MC96.1: type J (Fe-CuNi), type K (NiCr-Ni)
- Types of protection for use in hazardous locations: Intrinsic Safety (Ex ia) and non-Sparking (Ex nA)
- NEPSI approval (Ex ia)

Specs at a glance

- **Accuracy** class 2 acc. to IEC 60584
- **Response time** $t_{50} = 1 \text{ s}$ $t_{90} = 2 \text{ s}$
- **Max. process pressure (static)** at 20 °C: 25 bar (363 psi)
- **Operating temperature range** Type K: -40 °C ...1.100 °C (-40 °F ...2.012 °F) Type J: -40 °C ...750 °C (-40 °F ...1.382 °F)
- **Max. immersion length on request** up to 100.000,00 mm (3.937,01")

Field of application: The thermocouple (TC) cable probe is easy to install and provide a high operational safety due to reliable and accurate temperature measurement in common processes. The probe is specially suited to temperature measurement in machinery, laboratory equipment and plants in gaseous or liquid medium like air, water, oil, etc. Without additional thermowell the probe sheath is directly in contact with the process medium. This enables to detect rapid temperature changes fast and accurate.

Features and specifications

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

metric style

cable probe

suitable for hazardous areas

process connection as compression fitting

Thermowell / protection tube

without (not intended to use with thermowell)

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

2,0 mm (0,08")

3,0 mm (0,12")

4,5 mm (0,18")

6,0 mm (0,24")

Max. immersion length on request

up to 100.000,00 mm (3.937,01")

Material protection tube/ thermowell

1.4401 (316)

Alloy 600 (2.4816)

Thermometer

Process connection

compression fitting:

G1/4"

G3/8"

G1/2"

NPT1/4"

NPT1/2"

Tip shape

straight

Operating temperature range

Type K:

-40 °C ...1.100 °C

(-40 °F ...2.012 °F)

Type J:

-40 °C ...750 °C

(-40 °F ...1.382 °F)

Max. process pressure (static)

at 20 °C: 25 bar (363 psi)

Accuracy

class 2 acc. to IEC 60584

Thermometer

Response time

t50 = 1 s

t90 = 2 s

Integration head transmitter

no

Ex - approvals

ATEX II

NEPSI

IECEX

Certification

Gost Metrology

More information www.at.endress.com/TSC310