

## Proline Prowirl F 200 / 7F2B



More information and current pricing:

[www.at.endress.com/7F2B](http://www.at.endress.com/7F2B)

### Benefits:

- Integrated temperature measuring for mass/ energy flow of saturated steam
- Highest process safety – dualsens version enables redundant measurement
- High availability – proven robustness, resistance to vibrations, temperature shocks & water hammer
- No maintenance – lifetime calibration
- Convenient device wiring – separate connection compartment
- Safe operation – no need to open the device due to display with touch control, background lighting
- Integrated verification – Heartbeat Technology

### Specs at a glance

- **Max. measurement error** Volume flow (liquid):  $\pm 0.75\%$  Volume flow (steam, gas):  $\pm 1.00\%$  Mass flow (liquid):  $\pm 0.85\%$  Mass flow (steam, gas):  $\pm 1.7\%$
- **Measuring range** Liquid: 0.16 to 2412 m<sup>3</sup>/h (0.09 to 1420 ft<sup>3</sup>/min) depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F) Steam, gas: 2 to 32 166 m<sup>3</sup>/h (1.18 to 18 932 ft<sup>3</sup>/min) depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); air with 25 °C, 4.4 bar a (77 °F, 63.8 psi a)
- **Medium temperature range** Standard: -40 to +260 °C (-40 to +500 °F) High/low temperature (option): -200 to +400 °C (-328 to +752 °F) High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602 DSC sensor: 1.4435 (316/316L); UNS N06022 similar to Alloy C22, 2.4602 Connection: 1.4404 (F316/F316L); CX2MW similar to Alloy C22, 2.4602; 1.4408 (CF3M)

**Field of application:** The Prowirl F measuring tube is the first choice in heavy duty applications. The proven and patented capacitive DSC sensor ensures high precision measured values even under the toughest process conditions. Prowirl F 200 offers wetsteam detection and industry-compliant two-wire technology for seamless integration into existing infrastructures and control systems, as well as high operational safety in hazardous areas thanks to an intrinsically safe design, and a familiar installation procedure.

## Features and specifications

### Liquids

#### Measuring principle

##### Product headline

std\_productprofile\_product\_usp\_8110.

std\_productprofile\_product\_usp2\_38908\_1511797531.

Suitable for a wide range of applications; optimized for steam application:

##### Sensor features

std\_productprofile\_product\_benefits\_8113. High availability – proven resistance to vibrations, temperature shocks & water hammer.

std\_productprofile\_product\_benefits\_8115.

std\_productprofile\_product\_differentiating\_tech\_features\_6578.

std\_productprofile\_product\_differentiating\_tech\_features\_6577.

std\_successorproducts\_product\_differentiating\_tech\_features\_6580\_15

##### Transmitter features

Convenient device wiring – separate connection compartment. Safe operation to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology.

Display module with data transfer function. Robust dual-compartment housing for safety: worldwide approvals (SIL, Haz. area).

##### Nominal diameter range

DN 15 to 300 (½ to 12")

## Liquids

### Wetted materials

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602  
 DSC sensor: 1.4435 (316/316L); UNS N06022 similar to Alloy C22, 2.46  
 Connection: 1.4404 (F316/F316L); CX2MW similar to Alloy C22, 2.4602  
 (CF3M)

### Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow dif  
 temperature

### Max. measurement error

Volume flow (liquid):  $\pm 0.75$  %  
 Volume flow (steam, gas):  $\pm 1.00$  %  
 Mass flow (liquid):  $\pm 0.85$  %  
 Mass flow (steam, gas):  $\pm 1.7$  %

### Measuring range

Liquid: 0.16 to 2412 m<sup>3</sup>/h (0.09 to 1420 ft<sup>3</sup>/min)  
 depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)  
 Steam, gas: 2 to 32 166 m<sup>3</sup>/h (1.18 to 18 932 ft<sup>3</sup>/min)  
 depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); a  
 °C, 4.4 bar a (77 °F, 63.8 psi a)

### Max. process pressure

PN 40, Class 300, 20K

### Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)  
 High/low temperature (option): -200 to +400 °C (-328 to +752 °F)  
 High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

### Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)  
 Compact version (option): -50 to +80 °C (-58 to +176 °F)  
 Remote version (standard): -40 to +85 °C (-40 to +185 °F)  
 Remote version (option): -50 to +85 °C (-58 to +185 °F)

## Liquids

### Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

---

### Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

---

### Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

---

### Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

### Outputs

4-20 mA HART (passive)

4-20 mA (passive)

Pulse/frequency/switch output (passive)

---

### Inputs

Current Input 4-20 mA (passive)

---

### Digital communication

HART, PROFIBUS PA, FOUNDATION Fieldbus

---

### Power supply

DC 12 to 35 V (4-20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4-20 mA HART, 4-20 mA)

DC 12 to 35 V (4-20 mA HART, pulse/frequency/switch output, 4-20 mA)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, EAC

---

### Other approvals and certificates

---

## Liquids

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025). Heartbeat Technology complies with the requirements for measurement technology according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

### Pressure approvals and certificates

PED, CRN, AD 2000

### Material certificates

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614-1 similar to ASME IX (on request)

## Gas

### Measuring principle

#### Product headline

std\_productprofile\_product\_usp\_8110.

std\_productprofile\_product\_usp2\_38908\_1511797531.

Suitable for a wide range of applications; optimized for steam applications

#### Sensor features

std\_productprofile\_product\_benefits\_8113. High availability – proven resistance to vibrations, temperature shocks & water hammer.

std\_productprofile\_product\_benefits\_8115.

std\_productprofile\_product\_differentiating\_tech\_features\_6578.

std\_productprofile\_product\_differentiating\_tech\_features\_6577.

std\_successorproducts\_product\_differentiating\_tech\_features\_6580\_15

## Gas

**Transmitter features**

Convenient device wiring – separate connection compartment. Safe operation need to open the device due to display with touch control, background light. Integrated verification – Heartbeat Technology.

Display module with data transfer function. Robust dual-compartment housing safety: worldwide approvals (SIL, Haz. area).

**Nominal diameter range**

DN 15 to 300 (½ to 12")

**Wetted materials**

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602  
DSC sensor: 1.4435 (316/316L); UNS N06022 similar to Alloy C22, 2.46  
Connection: 1.4404 (F316/F316L); CX2MW similar to Alloy C22, 2.4602 (CF3M)

**Measured variables**

Volume flow, mass flow, corrected volume flow, energy flow, heat flow differential temperature

**Max. measurement error**

Volume flow (liquid): ±0.75 %

Volume flow (steam, gas): ±1.00 %

Mass flow (liquid): ±0.85%

Mass flow (steam, gas): ±1.7 %

**Measuring range**

Liquid: 0.16 to 2412 m<sup>3</sup>/h (0.09 to 1420 ft<sup>3</sup>/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 2 to 32 166 m<sup>3</sup>/h (1.18 to 18 932 ft<sup>3</sup>/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); a °C, 4.4 bar a (77 °F, 63.8 psi a)

**Max. process pressure**

PN 40, Class 300, 20K

---

**Gas****Medium temperature range**

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

---

**Ambient temperature range**

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

---

**Sensor housing material**

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

---

**Transmitter housing material**

AlSi10Mg, coated; 1.4404 (316L)

---

**Degree of protection**

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Outputs**

4-20 mA HART (passive)

4-20 mA (passive)

Pulse/frequency/switch output (passive)

---

**Inputs**

Current input 4-20 mA (passive)

---

**Digital communication**

HART, PROFIBUS PA, FOUNDATION Fieldbus

---

**Gas****Power supply**

DC 12 to 35 V (4-20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4-20 mA HART, 4-20 mA)

DC 12 to 35 V (4-20 mA HART, pulse/frequency/switch output, 4-20 mA)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

**Hazardous area approvals**

ATEX, IECEx, cCSAus, EAC

**Other approvals and certificates****Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025). Heartbeat Technology complies with the requirements for measurement technology according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

**Pressure approvals and certificates**

PED, CRN, AD 2000

**Material certificates**

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614-1 similar to ASME IX (on request)

**Steam****Measuring principle****Product headline**

std\_productprofile\_product\_usp\_8110.

std\_productprofile\_product\_usp2\_38908\_1511797531.

Suitable for a wide range of applications; optimized for steam applications



## Steam

### Sensor features

std\_productprofile\_product\_benefits\_8113. High availability – proven ro resistance to vibrations, temperature shocks & water hammer.

std\_productprofile\_product\_benefits\_8115.

std\_productprofile\_product\_differentiating\_tech\_features\_6578.

std\_productprofile\_product\_differentiating\_tech\_features\_6577.

std\_successorproducts\_product\_differentiating\_tech\_features\_6580\_15

### Transmitter features

Convenient device wiring – separate connection compartment. Safe opera need to open the device due to display with touch control, background ligl Integrated verification – Heartbeat Technology.

Display module with data transfer function. Robust dual-compartment ho safety: worldwide approvals (SIL, Haz. area).

### Nominal diameter range

DN 15 to 300 (½ to 12")

### Wetted materials

Measuring tube: 1.4408 (C3FM); CX2MW similar to Alloy C22, 2.4602

DSC sensor: 1.4435 (316/316L); UNS N06022 similar to Alloy C22, 2.46

Connection: 1.4404 (F316/F316L); CX2MW similar to Alloy C22, 2.4602 (CF3M)

### Measured variables

Volume flow, mass flow, corrected volume flow, energy flow, heat flow dif temperature

### Max. measurement error

Volume flow (liquid):  $\pm 0.75$  %

Volume flow (steam, gas):  $\pm 1.00$  %

Mass flow (liquid):  $\pm 0.85$  %

Mass flow (steam,, gas):  $\pm 1.7$  %

## Steam

### Measuring range

Liquid: 0.16 to 2412 m<sup>3</sup>/h (0.09 to 1420 ft<sup>3</sup>/min)

depending on medium: water with 1 bar a, 20 °C (14.5 psi a, 68 °F)

Steam, gas: 2 to 32 166 m<sup>3</sup>/h (1.18 to 18 932 ft<sup>3</sup>/min)

depending on medium: steam with 180 °C, 10 bar a (356 °F, 145 psi a); a  
°C, 4.4 bar a (77 °F, 63.8 psi a)

### Max. process pressure

PN 40, Class 300, 20K

### Medium temperature range

Standard: -40 to +260 °C (-40 to +500 °F)

High/low temperature (option): -200 to +400 °C (-328 to +752 °F)

High/low temperature (on request): -200 to +450 °C (-328 to +842 °F)

### Ambient temperature range

Compact version (standard): -40 to +80 °C (-40 to +176 °F)

Compact version (option): -50 to +80 °C (-58 to +176 °F)

Remote version (standard): -40 to +85 °C (-40 to +185 °F)

Remote version (option): -50 to +85 °C (-58 to +185 °F)

### Sensor housing material

Sensor connection housing: AlSi10Mg, coated; 1.4408 (CF3M)

### Transmitter housing material

AlSi10Mg, coated; 1.4404 (316L)

### Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version: IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, type 4X enclosure

### Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Steam****Outputs**

4-20 mA HART (passive)

4-20 mA (passive)

Pulse/frequency/switch output (passive)

---

**Inputs**

Current input 4-20 mA (passive)

---

**Digital communication**

HART, PROFIBUS PA, FOUNDATION Fieldbus

---

**Power supply**

DC 12 to 35 V (4-20 mA HART with/without pulse/frequency/switch output)

DC 12 to 30 V (4-20 mA HART, 4-20 mA)

DC 12 to 35 V (4-20 mA HART, pulse/frequency/switch output, 4-20 mA)

DC 9 to 32 V (PROFIBUS PA, pulse/frequency/switch output)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, EAC

---

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025). Heartbeat Technology complies with the requirements for measurement management according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

PED, CRN, AD 2000

---

**Material certificates**

3.1 material

NACE MR0175/MR0103, PMI (on request); welding test acc. to ISO 15614 similar to ASME IX (on request)

---

More information [www.at.endress.com/7F2B](http://www.at.endress.com/7F2B)