

Electronic differential pressure Deltabar FMD71

Electronic differential pressure system
utilizing two ceramic sensor modules and one
transmitter



Benefits:

- Eliminates traditional mechanical issues resulting in greater process availability and reliability
- Overload-resistant high purity ceramic sensor (99.9% Al₂O₃)
- Safety risks are minimized with the new electronic differential pressure system architecture and design
- Lowest total cost of ownership due to reduced installation time, maintenance, downtime and spare requirements
- Multivariable level measurement: HART-based differential pressure, head pressure and sensor temperatures from one system
- Continuous health indication of the entire system via HART-based diagnostic
- High reproducibility and long-term stability

More information and current pricing:

www.au.endress.com/FMD71

Specs at a glance

- **Accuracy** 0.075% of individual sensor, "PLATINUM" 0.05% of individual sensor
- **Process temperature** -25...+150°C (-13...+302°F)
- **Pressure measuring range** 100mbar...40bar (1.5psi...600psi)
- **Process pressure absolute / max. overpressure limit** 60 bar (900 psi)
- **Material process membrane** Ceramic 316L, AlloyC

Field of application: The electronic dp Deltabar FMD71 is a differential pressure system, used to measure the pressure or level, volume or mass of liquids in pressurized tanks or distillation columns/evaporators. The high pressure sensor (HP) measures the hydrostatic pressure. The low

pressure sensor (LP) measures the head pressure. The level is calculated in the transmitter using these two digital values. The electronic dp system eliminates issues of traditional differential pressure measurements.

Features and specifications

Pressure

Measuring principle

Differential pressure

Characteristic

Electronic differential pressure transmitter with ceramic sensor (Ceraphire) for level, volume or mass measurement in liquids.

Supply voltage

4...20 mA HART:

12...45V DC (Non Ex)

Ex ia: 12...30V DC

Reference Accuracy

0.075% of individual sensor,

"PLATINUM" 0.05% of individual sensor

Long term stability

0.05% of URL/year of individual sensor

Process temperature

-25...+150°C

(-13...+302°F)

Ambient temperature

-40...+80°C

(-40...+176°F)

Pressure

Measuring cell

100 mbar...40 bar
(1.5 psi...600 psi)

Vacuum resistance

0 mbar

Max. Turn down

100 : 1

Max. overpressure limit

60 bar (900 psi)

Process connection

Threads
Flansch (DIN, ASME, JIS)

Process connection hygienic

DIN11851

DIN11864-1

Tri-Clamp

DRD

Varivent

Material process membrane

Ceramic

316L, AlloyC

Material gasket

Viton, Kalrez, EPDM, NBR, Silicone

Fill fluid

Silicone Oil

Pressure**Material housing**

Die-cast aluminum

Stainless steel

Communication

4...20 mA HART

Certificates / Approvals

ATEX, FM, CSA, IECEx, NEPSI, INMETRO

Design approvals

NACE MR0175,

EN10204-3.1,

Hygienic approvals

EHEDG,

3A

Continuous / Liquids**Measuring principle**

Differential pressure

Characteristic / Application

Electronic differential pressure transmitter with ceramic sensor (Ceraphire) for level, volume or mass measurement in liquids.

Supply / Communication

4...20 mA HART:

12...45V DC

Exia: 12...30V DC

Continuous / Liquids**Accuracy**

0.075% of individual sensor,

"PLATINUM" 0.05% of individual sensor

Long term stability

0.05% of URL/year of individual sensor

Ambient temperature

-40...+80°C

(-40...+176°F)

Process temperature

-25...+150°C

(-13...+302°F)

Process pressure absolute / max. overpressure limit

60 bar (900 psi)

Pressure measuring range

100mbar...40bar

(1.5psi...600psi)

Process connection

Threads

Flanges (DIN, ASME, JIS)

Continuous / Liquids**Process connection hygienic**

DIN11851

DIN11864-1

Tri-Clamp

DRD

Varivent

Communication

4...20 mA HART

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, NEPSI, INMETRO

Design approvals

NACE MR0175

EN10204-3.1

Hygienic approvals

FDA

3A

Options

4-line digital display

SS- or Aluminium housing

Application limits

Use Software Applicator Sizing Electronic DP

More information www.au.endress.com/FMD71