

Digital ORP sensor Ceragel CPS72D

Memosens glass electrode for the chemical and life sciences industries



More information and current pricing:

www.au.endress.com/CPS72D

Benefits:

- Sensor resists strong acids and bases and high organic loads
- Suitable for CIP/SIP and autoclaving maintaining high accuracy
- Free from animal-based materials and from acrylamide
- Maximum process safety through non-contact inductive signal transmission
- Enables predictive maintenance due to storage of sensor and process-specific data
- Reduced operating costs thanks to minimized process downtime and extended sensor lifetime

Specs at a glance

- **Measurement range** -1500mV - +1500mV
- **Process temperature** -15°C - 140°C
- **Process pressure** max. 16bar

Field of application: Ceragel CPS72D is the digital specialist for demanding processes and hygienic applications. Its contamination-resistant gel guarantees stable measurement even in flowing media or low conductivity. The sensor measures reliably at high temperatures and is non-toxic assuring highest safety. Ceragel CPS72D is not the latest Memosens generation. To get information on the new Memosens CPS72E sensor with extended functionality, click [here](#).

Features and specifications

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

- Hygiene and sterile applications.- Pharmaceuticals, biotechnology, fermenters, contaminating media.

Characteristic

- Digital electrode with Memosens-Technology.- Gel-compact-electrode with ceramic diaphragm.- Platinum-cap- CIP/SIP and autoclavable- high accuracy

Measurement range

-1500mV - +1500mV

Measuring principle

- ceramic diaphragm- double chamber and double gel reference- Platinum-ring

Dimension

Diameter : 12mm Shaft length : 120,225,360mm

Process temperature

-15°C - 140°C

Process pressure

max. 16bar

Ex certification

ATEX

FM

CSA

Connection

Inductive transmission of digital measuring signals.

Ingres protection

IP68

ORP / Redox

Additional certifications

EHEDG

More information www.au.endress.com/CPS72D