

Radar measurement Time-of-Flight Micropilot FMR54

For level measurement in liquids where strong steam or ammonia can occur



More information and current pricing:

www.au.endress.com/FMR54

Benefits:

- Hardware and software developed according to IEC 61508 up to SIL3 (in homogeneous redundancy)
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even in the presence of obstructions in the vessel due to new Multi-Echo Tracking evaluation
- Reliable measurement even for changing product and process conditions
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test concept for SIL and WHG saves time and cost

Specs at a glance

- **Accuracy** +/- 6 mm (0.24 in)
- **Process temperature** -60...+400°C (-76...+752°F)
- **Process pressure absolute / max. overpressure limit**
Vacuum...160 bar (Vacuum...2320 psi)
- **Max. measurement distance** Standard: 20 m (65 ft) Planar antenna in stilling well: 38 m (125 ft)
- **Main wetted parts** 316L

Field of application: Micropilot FMR54 is prepared for the use in high temperature and high pressure applications and with the specially designed planar antenna it is particularly suited for stilling well

applications. The FMR54 free space radar is used for continuous, non-contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors.

Features and specifications

Continuous / Liquids

Measuring principle

Level radar

Characteristic / Application

Continuous non-contact level measurement for use in high-pressure and high-temperature applications,

Horn or planar antenna

Specialities

Heartbeat Technology,

SIL 2 according to IEC 61508,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

Safety and reliability with Multi-Echo Tracking,

HistoROM,

RFID TAG for easy identification

Supply / Communication

2-wire (HART / PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

Continuous / Liquids**Frequency**C-band (~6 GHz)

Accuracy+/- 6 mm (0.24 in)

Ambient temperature

-50...+80 °C

(-58...+176 °F)

Process temperature

-60...+400°C

(-76...+752°F)

Process pressure absolute / max. overpressure limit

Vacuum...160 bar

(Vacuum...2320 psi)

Main wetted parts316L

Process connection

Flange:

DN80...DN300,

ASME 3"...12",

JIS 10K, 20K

Max. measurement distance

Standard: 20 m (65 ft)

Planar antenna in stilling well: 38 m (125 ft)

Continuous / Liquids**Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC

Safety approvals

Overfill protection WHG

SIL

Design approvals

EN 10204-3.1

NACE MR0175, MR0103

ASME B31.3

AD2000

Marine approval

GL/ ABS/ LR/ BV/ DNV

Continuous / Liquids

Options

Display,

Customized parameterization,

Remote operation via SmartBlue App using Bluetooth®,

PWIS free,

Gastight feed through

Application limits

Maximum measuring range is dependent on the tank form and/or application

Free space with nozzle:
FMR51, FMR52, FMR53

Stilling well with ball valve:
FMR51, FMR52

Hygiene requirements:
FMR52, FMR53

316L or Alloy C non-resistant:
FMR52, FMR53

More information www.au.endress.com/FMR54