

Deltabar PMD55B - differential pressure transmitter

Smart transmitter with metal membrane for differential pressure monitoring in liquids and gases



More information and current pricing:

www.au.endress.com/PMD55B

Benefits:

- Wireless control of the device in the process area with the SmartBlue App without interrupting the process
- Reduce on site accidents and protect equipment when instruments are in difficult to reach areas
- Reduce systematic failures - error free SIL commissioning and instrument guided proof testing

Specs at a glance

- **Accuracy** Standard: up to 0.075 % Platinum: up to 0.055 %
- **Process temperature** -40°C...+110°C (-40°F...+230°F)
- **Pressure measuring range** 30 mbar.... 40 bar (0.45 psi... 600 psi)
- **Main wetted parts** 316L, AlloyC
- **Material process membrane** 316L, AlloyC

Field of application: This transmitter belongs to the new Deltabar generation. It is robust and easy to operate either locally or remotely. The transmitter can be controlled wireless via app on a mobile device using a secure Bluetooth connection. The PMD55B allows condition-based maintenance which increases efficiency in technical service significantly. The software is designed to simplify the handling. Intuitive wizards guide you through the setup and proof testing of the device which minimizes operating errors.

Features and specifications

Pressure

Measuring principle

Differential pressure

Characteristic

Transmitter with metal membrane for differential pressure monitoring in liquids or gases.

Intuitive and clear wizard for commissioning

Supply voltage

Ex d, Ex e, non-Ex:

10.5...35V DC

Ex i: 10.5...30V DC

Reference Accuracy

Standard:

up to 0.075 %

Platinum:

up to 0.055 %

Long term stability

0.05 % of URL/ year

0.13 % of URL/ 5 years

0.23 % of URL/ 10 years

Process temperature

-40°C...+110°C

(-40°F...+230°F)

Ambient temperature

-40°C...+85°C

(-40°F...+185°F)

Measuring cell

30 mbar...40 bar

(0.45 psi...600 psi)

Smallest calibratable span

0.3 mbar (0.0045 psi)

Pressure

Max. Turn down

100:1

Max. overpressure limit

250 bar (3750 psi)

Process connectionNPT1/4-18,
RC1/4"**Material process membrane**

316L, AlloyC

Material gasket

PTFE, FKM, EPDM, FFKM

Fill fluidSilicone oil,
Inert oil**Material housing**

Aluminium

Communication

4...20 mA HART

Certificates / Approvals

ATEX, CSA, IECEx, JPN Ex, INMETRO, NEPSI, UK Ex

Safety approvals

SIL

Design approvalsEN10204-3.1,
NACE MR0175,
NACE MR0103**Drinking water approvals**

NSF, KTW

Pressure

Specialities

Bluetooth® Operation and maintenance SmartBlue App,
RFID TAG for easy identification,
Plug and play functionalities

Continuous / Liquids

Measuring principle

Differential pressure

Characteristic / Application

Transmitter with metal membrane for differential pressure monitoring in liquids or gases.

Intuitive and clear wizard for commissioning

Specialities

Bluetooth® Operation and maintenance with SmartBlue App,
RFID TAG for easy identification,
Plug and play functionalities

Supply / Communication

Ex d, Ex e, non-Ex::

10.5...35V DC

Ex i: 10.5...30V DC

Accuracy

Standard:

up to 0.075 %

Platinum:

up to 0.055 %

Long term stability

0.05 % of URL/ year

0.13 % of URL/ 5 years

0.23 % of URL/ 10 years

Ambient temperature

-40°C...+85°C (-40°F...+185°F)

Continuous / Liquids**Process temperature**

-40°C...+110°C (-40°F...+230°F)

Process pressure / max. overpressure limit

250 bar (3750 psi)

Pressure measuring range

30 mbar.... 40 bar (0.45 psi... 600 psi)

Main wetted parts

316L, AlloyC

Process connection

NPT 1/4-18, RC1/4"

Communication

4...20 mA HART

Certificates / Approvals

ATEX, CSA, IECEX, JPN Ex, INMETRO, NEPSI, UK Ex

Safety approvals

SIL

Design approvals

EN 10204-3.1,
NACE MR0175,
NACE MR0103,
AD2000

Drinking water approvals

NSF, KTW

Application limits

None

Liquids

Measuring principle

Differential pressure

Product headline

Transmitter with metal membrane for differential pressure monitoring in liquids or gases.

Intuitive and clear wizard for commissioning

Sensor features

Fill fluid:

Inert oil,

Silicone oil

Transmitter features

Bluetooth® Operation and maintenance SmartBlue App,

RFID TAG for easy identification,

Plug and play functionalities

Wetted materials

316L, Alloy

Measuring range

30 mbar...40 bar

(0.45 psi...600 psi)

Medium temperature range

-40°C...+110°C

(-40°F...+230°F)

Ambient temperature range

-40°C...+85°C

(-40°F...+185°F)

Transmitter housing material

Aluminium

Display/Operation

Configuration via local display and operating tools possible

Remote display available

Liquids**Outputs**

4...20 mA HART

Digital communication

HART

Hazardous area approvals

ATEX, CSA, IECEx

Functional safety

SIL

Material certificatesEN10204-3.1,
NACE MR0175,
NACE MR0103**Steam****Measuring principle**Differential
pressure**Gas****Measuring principle**

Differential pressure

Product headlineTransmitter with metal membrane for differential pressure monitoring in
liquids or gases.

Intuitive and clear wizard for Commissioning

Sensor features

Fill fluid:

Inert oil,

Silicone oil

Gas	Transmitter features Bluetooth® Operation and maintenance SmartBlue App, RFID TAG for easy identification, Plug and play functionalities
	Wetted materials 316L, Alloy
	Measuring range 30 mbar...40 bar (0.45 psi...600 psi)
	Medium temperature range -40°C...+110°C (-40°F...+230°F)
	Ambient temperature range -40°C...+85°C (-40°F...+185°F)
	Transmitter housing material Aluminium
	Display/Operation Configuration via local display and operating tools possible Remote display available
	Outputs 4...20 mA HART
	Digital communication HART
	Hazardous area approvals ATEX, CSA, IECEx, JPN Ex, INMETRO, NEPSI, UK Ex
	Functional safety SIL

Gas

Material certificates

EN10204-3.1,
NACE MR0175,
NACE MR0103
AD2000

More information www.au.endress.com/PMD55B