

# TST187

## Modular RTD thermometer

Comprehensive and common temperature measurement technology for almost all branches of industry



from **€81.00**

Price as of 16.09.2021

More information and current pricing:

[www.be.endress.com/TST187](http://www.be.endress.com/TST187)

### Benefits:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Extension neck to protect the head transmitter from overheating
- Fast response time

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751
- **Response time**  $t_{50} = 18\text{ s}$   $t_{90} = 55\text{ s}$
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** PT 100: -50 °C ...400 °C (-58 °F ... 752 °F)
- **Max. immersion length on request** up to 400,00 mm (15,75")

**Field of application:** The thermometer is mainly used in the chemical industry but also finds its use in other branches. The device is equipped with a directly wired Pt100-sensor with 4-wire installation. A variety of process connections, immersion lengths and materials offer flexible application possibilities.

### Features and specifications

Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

metric style

modular temperature assembly

threaded process connection

with neck

incl. thermowell / protection tube  
(metal)

---

**Thermowell / protection tube**

welded protection tube

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

9,0 mm (0,35")

---

**Max. immersion length on request**

up to 400,00 mm (15,75")

---

**Material protection tube/ thermowell**

1.4404 (316L)

---

**Process connection**

male thread:

G1/2"

NPT1/2"

---

**Tip shape**

straight

---

**Surface roughness Ra**0,8  $\mu\text{m}$  (31,5  $\mu\text{in.}$ )

## Thermometer

---

**Operating temperature range**

PT 100:

-50 °C ...400 °C

(-58 °F ... 752 °F)

---

**Max. process pressure (static)**at 20 °C: 50 bar (725 psi)

---

**Accuracy**class A acc. to IEC 60751

---

**Response time**

t50 = 18 s

t90 = 55 s

---

**Integration head transmitter**no

---

More information [www.be.endress.com/TST187](http://www.be.endress.com/TST187)