

Proline Promag W 400 elektromagnetische flowmeter

Veelzijdige standaardflowmeter voor de water- en afvalwaterindustrie



Voordelen:

- Betrouwbare meting met constante nauwkeurigheid met een inlaatlengte van 0 x DN en geen drukverlies
- Flexibele techniek – sensor met vaste of lap-joint procesaansluitingen
- Toepassingsgeschiktheid – corrosiebescherming volgens EN ISO 12944 voor ondergrondse installaties of onderwaterinstallaties
- Verbeterde beschikbaarheid van de installatie – sensor voldoet aan de specifieke eisen van de industrie
- Veilige bediening – geen noodzaak om het instrument te openen
- Tijdbesparende lokale bediening zonder aanvullende software en hardware – geïntegreerde webserver
- Geïntegreerde verificatie en aangroeidetectie – Heartbeat Technology

Meer informatie en actuele prijzen:

www.be.endress.com/5W4C

Overzicht specificaties

- **Max. meetfout** Volume flow (standard): $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s) Volume flow (option): $\pm 0.2\%$ o.r. ± 2 mm/s (0.08 in/s), Flat Spec
- **Measuring range** 9 dm³/min to 162 000 m³/h (2.5 gal/min to 100 000 gal/min)
- **Medium temperature range** Liner material hard rubber: 0 to +80 °C (+32 to +176 °F) Liner material polyurethane: -20 to +50 °C (-4 to +122 °F) Liner material PTFE: -20 to +90 °C (-4 to +194 °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Liner material hard rubber: 0 to +80 °C (+32 to +176 °F) Liner material polyurethane: -20 to +50 °C (-4 to +122 °F) Liner material PTFE: -20 to +90 °C (-4 to +194 °F) Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

Toepassingsgebied: Met zijn internationale goedkeuringen voor custody transfer en drinkwater is de Promag W geschikt voor de meest uiteenlopende toepassingen. Het instrument is als compacte uitvoering en als remote uitvoering leverbaar. De Promag W 400 bespaart u tijd en geld dankzij de brede functionaliteit van de transmitter, die voor water en afvalwater is geoptimaliseerd. Bovendien garandeert de Heartbeat Technology betrouwbare metingen en verificaties volgens de regels.

Kenmerken en specificaties

Liquids

Meetprincipe

Electromagnetic

Product headline

Versatile standard flowmeter for the water and wastewater industry. Reliable measurement at constant accuracy with 0 x DN inlet run and no pressure loss.

Ideal for water measurement, e.g. drinking water, utility water and industrial/municipal wastewater.

Sensor features

Flexible engineering – sensor with fixed or lap-joint process connections. Application fitness – EN ISO 12944 corrosion protection for underground or underwater installation. Improved plant availability – sensor compliant with industry-specific requirements.

International drinking water approvals. Degree of protection IP68 (Type 6P enclosure). Approved for custody transfer to MI-001/OIML R49.

Transmitter features

Safe operation – no need to open the device due to display with touch control, background lighting. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology.

Transmitter housing made of durable polycarbonate or aluminium. WLAN access. Integrated data logger: measured values monitoring.

Liquids

Nominal diameter range

DN 25 to 2400 (1 to 90")

Wetted materials

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Liner material PTFE: -20 to +90 °C (-4 to +194 °F)

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

Measured variables

Volume flow, conductivity, mass flow

Max. meetfoutVolume flow (standard): ± 0.5 % o.r. ± 1 mm/s (0.04 in/s)Volume flow (option): ± 0.2 % o.r. ± 2 mm/s (0.08 in/s), Flat Spec**Measuring range**9 dm³/min to 162 000 m³/h (2.5 gal/min to 100 000 gal/min)**Max. process pressure**

PN 40, Class 300, 20K

Medium temperature range

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Liner material PTFE: -20 to +90 °C (-4 to +194 °F)

Ambient temperature range

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Sensor housing material

DN 25 to 300 (1 to 12"): AlSi10Mg, coated

DN 25 to 2000 (1 to 78"): Carbon steel with protective varnish

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): Polycarbonate

Transmitter housing material

Polycarbonat; AlSi10Mg, coated

Liquids

Degree of protection

Compact version: IP66/67, type 4X enclosure

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP68, type 6P enclosure, with protective varnish

according to EN ISO 12944 C5 - M/Im1/Im2/Im3

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display, web browser and operating tools possible

Outputs

3 outputs:

0 - 20 mA/4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Pulse/frequency output (passive)

Switch output (passive)

Inputs

Status input

Digital communication

HART, PROFIBUS DP, EtherNet/IP, Modbus RS485

Power supply

AC 100...240 V / AC/DC 24 V

Hazardous area approvals

cCSAus

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Custody transfer according to MI - 001 or OIML R49 (optional class I in combination with ODN inlet run)

Liquids

Pressure approvals and certificates

CRN

Material certificates

3.1 material

Hygienic approvals and certificates

Drinking water approval: ACS, KTW/W270, NSF 61, WRAS BS 6920

Meer informatie www.be.endress.com/5W4C