

Proline Promass F 100 Coriolis-flowmeter

Robuuste, uiterst nauwkeurig metende
flowmeter met ultracompacte transmitter



Meer informatie en actuele prijzen:

www.be.endress.com/8F1B

Voordelen:

- Maximale procesveiligheid – ongevoelig voor wisselende en zware omstandigheden
- Minder procesmeetpunten – multivariabele meting (flow, dichtheid, temperatuur)
- Ruimtebesparende installatie – geen in-/uitlaatlengten
- Ruimtebesparende transmitter – volledige functionaliteit in een zeer kleine ruimte
- Tijdbesparende lokale bediening zonder aanvullende software en hardware – geïntegreerde webserver
- Geïntegreerde verificatie – Heartbeat Technology

Overzicht specificaties

- **Max. meetfout** Mass flow (liquid): $\pm 0.1\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.1\%$ Mass flow (gas): $\pm 0.25\%$ Density (liquid): $\pm 0.0005\text{ g/cm}^3$
- **Measuring range** 0 to 2 200 000 kg/h (0 to 80 840 lb/min)
- **Medium temperature range** Standard: -50 to $+150\text{ }^\circ\text{C}$ (-58 to $+302\text{ }^\circ\text{F}$) Option: -50 to $+240\text{ }^\circ\text{C}$ ($-58\text{...}+464\text{ }^\circ\text{F}$)
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022) Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Toepassingsgebied: De Promass F staat al lang bekend als een zeer nauwkeurig instrument onder de meest uiteenlopende procesomstandigheden. Het instrument is geschikt voor een breed scala aan toepassingen. Samen met de kleinste transmitter die op dit moment verkrijgbaar is, levert het instrument uitstekende prestaties in een zeer

kleine ruimte. De Promass F 100 heeft de voorkeur van systeemintegrators, skidbouwers en productfabrikanten. Het instrument is leverbaar met een ultracompacte hygiënische roestvrijstalen behuizing, waardoor het zelfs in de meest compacte installaties kan worden geplaatst.

Kenmerken en specificaties

Density/Concentration

Meetprincipe

Coriolis

Product headline

Flowmeter with premium accuracy, robustness and an ultra-compact transmitter.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature up to $+240$ °C ($+464$ °F). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Density/Concentration**Wetted materials**

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. meetfout

Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Density/Concentration

Display/Operation

4 - line backlit display available (no local operation)
Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)
Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)
Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)
BV (Bureau Veritas)
LR (Lloyds Register)
BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Density/Concentration

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Gas

Meetprincipe

Coriolis

Product headline

Flowmeter with premium accuracy, robustness and an ultra-compact transmitter.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature up to $+240\text{ }^{\circ}\text{C}$ ($+464\text{ }^{\circ}\text{F}$). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

Nominal diameter rangeDN 8 to 250 ($\frac{3}{8}$ to 10")

Gas

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. meetfout

Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Gas

Display/Operation

4 - line backlit display available (no local operation)
Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)
Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)
Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)
BV (Bureau Veritas)
LR (Lloyds Register)
BV approval
CCS approval

Gas**Pressure approvals and certificates**

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Steam**Meetprincipe**

Coriolis

Product headline

Flowmeter with premium accuracy, robustness and an ultra-compact transmitter.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature up to $+240$ °C ($+464$ °F). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Space - saving transmitter – full functionality on the smallest footprint.

Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology.

Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

Steam

Nominal diameter rangeDN 8 to 250 ($\frac{3}{8}$ to 10")**Wetted materials**

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. meetfoutMass flow (liquid): ± 0.1 % (standard), 0.05 % (option)Volume flow (liquid): ± 0.1 %Mass flow (gas): ± 0.25 %Density (liquid): ± 0.0005 g/cm³**Measuring range**

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature rangeStandard: -50 to $+150$ °C (-58 to $+302$ °F)Option: -50 to $+240$ °C (-58 ... $+464$ °F)**Ambient temperature range**Standard: -40 to $+60$ °C (-40 to $+140$ °F)Option: -50 to $+60$ °C (-58 to $+140$ °F)**Sensor housing material**

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Steam**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

No local operation

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

InputsNone

Digital communicationHART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supplyDC 20 to 30 V

Hazardous area approvalsATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safetyCE, C-Tick, EAC marking

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Steam

Marine approvals and certificates

ABS (American Bureau of Shipping)
 BV (Bureau Veritas)
 LR (Lloyds Register)
 BV approval
 CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material
 NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME,
 NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Liquids

Meetprincipe

Coriolis

Product headline

Flowmeter with premium accuracy, robustness and an ultra-compact transmitter.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature up to $+240$ °C ($+464$ °F). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Liquids

Transmitter features

Space - saving transmitter – full functionality on the smallest footprint.
Time - saving local operation without additional software and hardware
– integrated web server. Integrated verification – Heartbeat Technology.
Robust, ultra-compact transmitter housing. Highest degree of protection:
IP69. Local display available.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume, flow, reference density, concentration

Max. meetfout

Mass flow (liquid): ± 0.1 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Liquids

Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304), 1.4404 (316L)

Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-Tick, EAC marking

Liquids

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

ABS (American Bureau of Shipping)

BV (Bureau Veritas)

LR (Lloyds Register)

BV approval

CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Meer informatie www.be.endress.com/8F1B