

Nitrite analyzer

Liquiline System CA80NO

Colorimetric system for monitoring of drinking water, mineral water or raw water for food production



Meer informatie en actuele prijzen:

www.be.endress.com/CA80NO

Voordelen:

- Compliance with standard colorimetric measuring principle - naphthylamine method - following ISO 6777 and DIN EN 26777 ensures comparability to lab measurements.
- Reduced operating costs through automatic calibration and cleaning.
- Simple maintenance: no tools required.
- Advanced diagnostics with remote access for increased process safety.
- Fast commissioning and plug & play thanks to Memosens technology and user-friendly operation.
- Easy upgrade of functionality - even to a complete measuring station - simply by adding modules and connecting Memosens sensors. Reduces installation effort.

Overzicht specificaties

- **Measurement range** 10 to 500 µg/l NO₂-N 0.2 to 3.0 mg/l NO₂-N 0.1 to 1.0 mg/l NO₂-N 0.1 to 1.0 mg/l with dilution function to maximum 5 to 50 mg/l NO₂-N
- **Process temperature** 4 to 40 °C (39 to 104 °F)
- **Process pressure** At atmospheric pressure, < 0.2 bar absolute

Toepassingsgebied: Liquiline System CA80NO offers precise, regulation-compliant online measurement of nitrite. It supports you in meeting the specified limits in drinking water, mineral water or food production. Like all Liquiline System analyzers, it enables plug & play of up to four Memosens sensors – minimizing the installation effort. Automatic calibration and cleaning and the low reagent consumption reduce

operating and maintenance costs. Advanced diagnostics with remote access ensure process safety.

Kenmerken en specificaties

Analyser

Meetprincipe

Colorimetric

Characteristic

Process analyzer for Nitrite in potable water

Size

Housing (open version):

793 x 530 x 417 mm

31.22 x 20.87 x 16.42 in

Housing (closed version):

793 x 530 x 463 mm

31.22 x 20.87 x 18.23 in

Housing with base:

1723 x 530 x 463 mm

67.83 x 20.87 x 18.23 in

Design

Open design, cabinet and stand housing

High-Performance plastic ASA-PC, additional stand coated steel

Process temperature

4 to 40 °C (39 to 104 °F)

Analyser

Ambient temperature

5 to 40 °C (41 to 104 °F)

Outdoor version: - 20 to 40 °C (-4 to 104 °F)

Process pressure

At atmospheric pressure, < 0.2 bar absolute

Sample flow rate

Min. 5 ml/min (0.17 fl.oz/min)

Consistency of the sample

Suspended solids content

Turbidity < 50 NTU, aqueous, homogenized

Specials

Easy upgrade to measuring station with up to four digital Memosens sensors

Automatic calibration and cleaning

User-configurable measuring, cleaning and calibration intervals

Optional cooling module for standard solution

2 channel version optional

User-definable measuring ranges

Modular design for easily extensible functionality

Application

Limit value monitoring of nitrite for potable water and mineral water applications

Power supply

100 to 120 VAC / 200 to 240 VAC ± 10%

24 VDC ± 10%

50 ± 1 or 60 ± 1,2 Hz

Analyser**Output / communication**

2x 0/4 to 20 mA
Modbus RS485/TCP (optional)
Ethernet (optional)
Alarmrelay

Input

1 or 2 measuring channel
1 to 4 digital sensor inputs for sensors with Memosens protocol (optional)

Measurement range

10 to 500 µg/l NO₂-N

0.2 to 3.0 mg/l NO₂-N

0.1 to 1.0 mg/l NO₂-N

0.1 to 1.0 mg/l with dilution function to maximum 5 to 50 mg/l NO₂-N

Consumables

Reagents and standard solutions CY80NO as well as cleaner CY800 are necessary for the operation
Regular maintenance is done with the parts of the maintenance kit CAV800

Meer informatie www.be.endress.com/CA80NO