

Teqwave I – Ultrasonic concentration meter

Smart, flexible insertion measuring device – individually for your process



Voordelen:

- Easy and efficient – real-time in situ liquid analysis
- Full transparency – constant monitoring of product quality without sampling
- Highest process safety – reliable metering due to robust, maintenance-free sensor
- Cost-saving – fewer measuring points due to multivariable measurement
- Customized usage – innovative application concept, expendable for changing measuring tasks
- Simplified process control – user-friendly operation and clear status visualization
- Local data backup – integrated data storage for measured values up to 7,5 years

Meer informatie en actuele prijzen:

www.be.endress.com/D9IB

Overzicht specificaties

- **Max. meetfout** Density: $\pm 0.01 \text{g/cm}^3$ Temperature: $\pm 0.5 \text{K}$ Sound velocity: 2m/s
- **Measuring range** Concentration According to concentration app data sheet, maximum 0 to 100 % Sound velocity 600 to 2000 m/s Temperature concentration app data sheet, maximum 0 to $+100 \text{ }^\circ\text{C}$ (32 to $+212 \text{ }^\circ\text{F}$) Density 0.7 to 1.5g/cm^3
- **Medium temperature range** 0 to $100 \text{ }^\circ\text{C}$ (32 to $212 \text{ }^\circ\text{F}$)
- **Max. process pressure** max. 16 bar at $20 \text{ }^\circ\text{C}$ (232 psi at $68 \text{ }^\circ\text{F}$)

Toepassingsgebied: The insertion measuring device Teqwave I was developed for accurate real-time liquid analysis in vessels and larger pipes. Dedicated to in situ concentration measurement, Teqwave monitors various measuring parameters at once, and thus reduces

operational expenditure. Match your Teqwave transmitter perfectly to your production needs: You can flexibly define and extend your application range.

Kenmerken en specificaties

Density/Concentration

Meetprincipe

Ultrasonic concentration

Product headline

Smart, flexible insertion measuring device – individually for your process. Easy and efficient – real-time in situ liquid analysis. Continuous concentration measurement of liquids in vessels or large pipes.

Sensor features

Full transparency – constant monitoring of product quality without sampling. Highest process safety – reliable metering due to robust, maintenance-free sensor. Cost-saving – fewer measuring points due to multivariable measurement.

Insertion length: 180 mm (7 in) or 500 mm (20 in). Accurate and independent of flow profile.

Transmitter features

Customized usage – innovative application concept, expendable for changing measuring tasks. Simplified process control – user-friendly operation and clear status visualization. Local data backup – integrated data storage for measured values up to 7,5 years.

Industry-compliant, easy installation via DIN rail. 3.5" TFT color touch screen or LED indication. 4-20 mA, Modbus TCP.

Nominal diameter range

Insertion length: 180 mm (7") or 500 mm (20")

Density/Concentration**Measured variables**

Concentration
Density
Sound velocity
Temperature

Max. meetfout

Density: $\pm 0.01 \text{ g/cm}^3$
Temperature: $\pm 0.5 \text{ K}$
Sound velocity: 2 m/s

Measuring range

Concentration According to concentration app data sheet, maximum 0 to 100 %
Sound velocity 600 to 2000 m/s
Temperature concentration app data sheet, maximum 0 to $+100 \text{ }^\circ\text{C}$ (32 to $+212 \text{ }^\circ\text{F}$)
Density 0.7 to 1.5 g/cm^3

Max. process pressure

max. 16 bar at $20 \text{ }^\circ\text{C}$ (232 psi at $68 \text{ }^\circ\text{F}$)

Medium temperature range

0 to $100 \text{ }^\circ\text{C}$ (32 to $212 \text{ }^\circ\text{F}$)

Ambient temperature range

0 to $+50 \text{ }^\circ\text{C}$ (32 to $122 \text{ }^\circ\text{F}$)

Sensor housing material

Stainless steel V4A 1.4571

Degree of protection

Sensor: IP68 (with cable plugged in), IP66 (without cable connector)
Transmitter: IP40

Display/Operation

LED status indication
TFT color touch display

Density/Concentration

Outputs

4-20mA / Modbus TCP

Power supply

DC 24 V (18 to 35 V)

Hazardous area approvals

Non-hazardous area

UK; Non-hazardous area

Product safety

CE, C-Tick

Meer informatie www.be.endress.com/D9IB