

Proline Prosonic Flow 93P ultrasone flowmeter

Flowmeter voor installatie in gevaarlijke omgevingen met een uitgebreid aantal analoge en digitale uitgangen



Meer informatie en actuele prijzen:

www.be.endress.com/93P

Voordelen:

- Automatische frequentiescan voor maximale meetprestaties
- Verhoogde veiligheid voor chemische & petrochemische industrie – internationale goedkeuringen voor gevaarlijke omgevingen
- Langdurig stabiel signaal - onderhoudsvrije permanente montage van buitenaf met koppelpads
- Procestransparantie – geschikt voor diagnose
- Maximale prestaties – uitgebreide functionaliteit en diagnose
- Flexibele gegevensoverdrachtopties – talrijke communicatietypen
- Automatisch herstel van gegevens voor onderhoud

Overzicht specificaties

- **Max. meetfout** Volume flow: $\pm 3\%$ o.r. for DN15 $\pm 2\%$ o.r. for DN25 to DN200 $\pm 2\%$ o.r. above DN200
- **Measuring range** 0.3 to 10 m/s (1 to 33 ft/s)
- **Medium temperature range** DN15 to 65 -40 to +100°C (-40 +212 °F) -40 to +150°C (-40 +302 °F) option DN50 to 4000 -40 to +80°C (-40 +276 °F) -40 to +170°C (-40 +338 °F) option
- **Max. process pressure** N/A
- **Wetted materials** Clamp on system: Sensor holder 1.4308/CF-8 Sensor housing 1.4301/304 Strapping bands 1.4301/304

Toepassingsgebied: De Prosonic Flow P clamp-on-sensor is speciaal ontworpen voor de procesindustrie. In combinatie met de Prosonic Flow 93-transmitter met aanraakbediening, 4-regelig display en uitgebreide functionaliteit biedt de Prosonic Flow 93P hoge nauwkeurigheid in standaardtoepassingen.

Kenmerken en specificaties

Liquids

Meetprincipe

Ultrasonic flow

Product headline

Flowmeter for hazardous area installations with a wide range of analog and digital outputs.

Automatic frequency scan for maximum measuring performance.

Ideal clamp-on device for applications with chemicals, solvents, liquid hydrocarbons, acids, alkalis.

Sensor features

Increased safety for chemical and petrochemical industry – international hazardous area approvals. Long-term stable signal – maintenance-free permanent mounting from outside with coupling pads. Process transparency – diagnostic capability.

Medium temperature: -40 to 170 °C (-40 to 338 °F). Wide nominal diameter range: DN 15 to 4000 (½ to 160"). Process piping unaffected by meter installation.

Transmitter features

Highest performance – extended functionality and diagnostics. Flexible data transfer options – numerous communication types. Automatic recovery of data for servicing.

Aluminium transmitter housing. 4 - line backlit display with touch control. HART, PROFIBUS PA/DP, FOUNDATION Fieldbus.

Nominal diameter range

Single channel, 1 or 2 paths : DN15 to 4000 (1/2 to 160")

Dual channel, 1 or 2 paths : DN15 to 4000 (1/2 to 160")

Wetted materials

Clamp on system:

Sensor holder 1.4308/CF-8

Sensor housing 1.4301/304

Strapping bands 1.4301/304

Liquids

Measured variables

Volume flow channel 1&2, average volume flow, volume flow difference, sound velocity, flow velocity, totalizer

Max. meetfout

Volume flow:

±3% o.r. for DN15

±2% o.r. for DN25 to DN200

±2% o.r. above DN200

Measuring range

0.3 to 10 m/s (1 to 33 ft/s)

Max. process pressure

N/A

Medium temperature range

DN15 to 65

-40 to +100°C (-40 +212 °F)

-40 to +150°C (-40 +302 °F) option

DN50 to 4000

-40 to +80°C (-40 +276 °F)

-40 to +170°C (-40 +338 °F) option

Ambient temperature range

-20 to +60 °C (-4 to +140 °F)

-40 to +60 °C (-40 to +140 °F) optional

Sensor housing material

N/A

Transmitter housing material

Wall-mounted housing: powder-coated die-cast aluminum

Degree of protection

IP67, type 4X for transmitter

IP68 type 6P for sensors. Transmitter: IP67, type 4X enclosure

Liquids

Display/Operation

4 lines backlit display with three optical keys

Outputs

1x 4-20 mA HART

1x Pulse/frequency/switch output (passive)

Inputs

N/A

Digital communication

HART

PROFIBUS PA

Profibus DP

FOUNDATION Fieldbus

Power supply

85 to 260 V AC

20 to 55 V AC

16 to 62V DC

Hazardous area approvals

ATEX, FM/CSA, NEPSI, JPN

Other approvals and certificates

Flowmeter verification for DN15, 25, 40, 50 & 100 only

Marine certificate

EAC marking

Product safety

EAC marking

Metrological approvals and certificates

Flowmeter verification for DN15, 25, 40, 50 & 100 only

Marine approvals and certificates

Marine certificate

Meer informatie www.be.endress.com/93P