

# Ceraphant T PTC31



## Benefícios:

- Integrated switching electronics for decentral and economic process monitoring and control
- Function check and information on site thanks to LEDs and digital display
- Dry capacitance ceramic sensor (Ceraphire)
- Overload-resistant high purity ceramic sensor (99.9% Al<sub>2</sub>O<sub>3</sub>)
- Best fit for vacuum applications and applications with abrasive media

## Especificações resumidas

- **Measuring cell** 100mbar...40bar (1.5psi...600psi)

Mais informações e preço atual:

[www.br.endress.com/PTC31](http://www.br.endress.com/PTC31)

**Campo de aplicação:** The Ceraphant PTC31 is a price-attractive pressure switch with ceramic, vacuum tight measuring cell for safe measurement and monitoring of absolute and gauge pressure.

## Características e especificações

### Pressure

#### Measuring principle

#### Characteristic

Intelligent pressure switch with ceramic, vacuum tight measuring cell, longterm stable and overload resistant

#### Supply voltage

12...30VDC

#### Reference Accuracy

0,5%

#### Long term stability

0,15% of URL/year

## Pressure

**Process temperature**

-40°C...100°C  
(-40°F...212°F)

---

**Ambient temperature**

-40°C...85°C  
(-40°F...185°F)

---

**Measuring cell**

100mbar...40bar  
(1.5psi...600psi)

---

**Max. overpressure limit**

60bar (900psi)

---

**Process connection**

Threads

---

**Communication**

1x PNP switch  
2x PNP switch  
1x PNP switch + 4...20mA analogue

---

**Design approvals**

EN10204-3.1

---

**Specialities**

Digital display  
Robust SS-housing with Ra < 0,8 micron

---

Mais informações [www.br.endress.com/PTC31](http://www.br.endress.com/PTC31)