

TH12

US style RTD sensor, cable probe

Cost efficient RTD sensor designed for use in the process industry or factory automation



Mais informações e preço atual:

www.br.endress.com/TH12

Benefícios:

- High flexibility due to customized immersion length
- Fast response time with reduced/tapered tip form
- Simplified model structure: Competitively priced, offers great value. Easy to order and reorder
- Improved galvanic isolation on most devices (2 kV)

Especificações resumidas

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Response time** 63% rt = 2,0 s
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi) depends on configuration
- **Operating temperature range** PT100 WW: -200 °C ... 600 °C (-328 °F ... 1.112 °F) PT100 TF: -50 °C ... 200 °C (-58 °F ... 392 °F)
- **Max. immersion length on request** up to 96" (2439 mm) others on request

Campo de aplicação: The Pt100 cable probe is easy to install and provide a high operational safety due to reliable and accurate temperature measurement in common processes. Without additional thermowell the probe sheath is directly in contact with the process medium. This enables the cable probe to detect rapid temperature changes fast and accurate.

Características e especificações

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

US style

cable probe

process connection as compression fitting

without neck

Thermowell / protection tube

without (not intended to be used with thermowell)

Insert / probe

mineral insulated (MI), flexible

PTFE-insulated, rigid

Outer diameter protection tube / Insert

1/8" (3,18 mm)

3/16" (4,76 mm)

1/4" (6,35 mm)

3/8" (9,53 mm)

Max. immersion length on request

up to 96" (2439 mm)

others on request

Thermometer

Material protection tube/ thermowell

Sensor sheath

316/316L

Optional coating

Not applicable

Process connection

compression fitting:

NPT1/8"

NPT1/4"

Tip shape

straight

reduced

Surface roughness Ra

Not defined

Operating temperature range

PT100 WW:

-200 °C ... 600 °C

(-328 °F ... 1.112 °F)

PT100 TF:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

Thermometer**Max. process pressure (static)**

at 20 °C: 40 bar (580 psi)

depends on configuration

Accuracy

class A acc. to IEC 60751

class B acc. to IEC 60751

Response time63% rt = 2,0 s

Integration head transmitterNot applicable

Mais informações www.br.endress.com/TH12