

# Radiometric level and density measurement Gamma Source FSG61

Gamma radiation source ( $^{60}\text{Co}$ ) for radiometric level, point level, density and interface measurement



## Benefícios:

- Specially constructed source capsule conforms to strictest safety requirements:  
Typically class C66646 to ISO 2919
- Point source in special source container ensures simple handling and easy installation
- Choice of activity ensures optimized dosage for your application
- High penetration energy even for extreme applications

## Especificações resumidas

- **Process temperature** Any
- **Process pressure absolute / max. overpressure limit** Any

Mais informações e preço atual:

[www.br.endress.com/FSG61](http://www.br.endress.com/FSG61)

**Campo de aplicação:** The Gamma Source FSG61 is specially suited for level applications with thick tank walls, high pressure or for density applications with big pipe diameters and large density ranges thanks to its high penetration energy.

## Características e especificações

Point Level / Solids

**Measuring principle**

Radiometric Limit

---

**Point Level / Solids****Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with

Applicator

---

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Process temperature**

Any

---

**Process pressure absolute / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Density****Measuring principle**

Radiometric Density

---

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Density**

---

**Process temperature**Any

---

**Process pressure absolute**Any

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO

2919

Activity calculation with

Applicator

---

**Point Level / Liquids****Measuring principle**Radiometric Limit

---

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with

Applicator

---

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

---

**Process temperature**Any

---

**Point Level / Liquids****Process pressure absolute / max. overpressure limit**

Any

**Components**

Installed in source container

**Continuous / Solids****Measuring principle**

Radiometric

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

Activity calculation with

Applicator

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

**Process temperature**

Any

**Process pressure absolute / max. overpressure limit**

Any

**Components**

Installed in source container

**Continuous / Liquids****Measuring principle**

Radiometric

**Characteristic / Application**

Source

Isotope: Cobalt 60

Half-life: 5.3 years

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO 2919

**Ambient temperature**

-20 °C ... 250 °C

(-4 °F ... 482 °F)

**Process temperature**

Any

**Process pressure absolute / max. overpressure  
limit**

Any

**Components**

Installed in source container

Mais informações [www.br.endress.com/FSG61](http://www.br.endress.com/FSG61)