

# TH15

## Modular RTD thermometer, US style

### Best in class temperature measurement for general applications



Mais informações e preço atual:

[www.br.endress.com/TH15](http://www.br.endress.com/TH15)

#### Benefícios:

- High flexibility due to modular assembly with standard terminal heads and customized immersion length
- One source shopping for temperature measurement solutions. World class transmitter with integrated sensor offering for heavy process industry applications. Remove and install straight out of the box!
- Improved galvanic isolation on most devices (2 kV)
- Simplified model structure: Competitively priced, offers great value. Easy to order and reorder. A single model number includes sensor and transmitter assembly for a complete point solution
- All iTEMP® transmitters provide long term stability  $\leq 0.05\%$  per year
- Fast response time with reduced/tapered tip form
- Head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

#### Especificações resumidas

- **Accuracy** class A acc. to IEC 60751 class B acc. to IEC 60751
- **Max. process pressure (static)** class AA acc. to IEC 60751 class A acc. to IEC 60751 class B acc. to IEC 60751
- **Operating temperature range** PT100 WW:  $-200\text{ °C} \dots 600\text{ °C}$  ( $-328\text{ °F} \dots 1.112\text{ °F}$ ) StrongSens:  $-50\text{ °C} \dots 500\text{ °C}$  ( $-58\text{ °F} \dots 932\text{ °F}$ ) PT100 TF:  $-50\text{ °C} \dots 200\text{ °C}$  ( $-58\text{ °F} \dots 392\text{ °F}$ )
- **Max. immersion length on request** up to 41" (1041 mm) others on request

**Campo de aplicação:** The robust device is a unit ready for use within and existing thermowell and includes various housing transmitter heads to meet the application and space requirement needs. The unit offers enhanced measurement accuracy and reliability. A variety of connections,

dimensions and materials (like 316L SS and Hastelloy C276) offer flexible application possibilities.

## Características e especificações

### Thermometer

**Measuring principle**

Resistance Temperature Detector

**Characteristic / Application**

Industrial US style  
modular temperature assembly  
with extension  
to be used with existing thermowell

**Thermowell / protection tube**

to be used with thermowell

**Insert / probe**

mineral insulated (MI), flexible  
PTFE-insulated, rigid

**Outer diameter protection tube / Insert**

Insert 1/4" (6,35 mm)

**Max. immersion length on request**

up to 41" (1041 mm)  
others on request

**Material protection tube/ thermowell**

Sensor sheath  
316/316L

**Optional coating**

Not applicable

---

**Thermometer****Process connection**

Schutzrohranschluss

Außen-Gewinde:

NPT1/2"

1-1/4"-18 UNEF

---

**Tip shape**

straight

---

**Surface roughness Ra**

Not defined

---

**Operating temperature range**

PT100 WW:

-200 °C ... 600 °C

(-328 °F ... 1.112 °F)

StrongSens:

-50 °C ... 500 °C

(-58 °F ... 932 °F)

PT100 TF:

-50 °C ... 200 °C

(-58 °F ... 392 °F)

---

**Max. process pressure (static)**

class AA acc. to IEC 60751

class A acc. to IEC 60751

class B acc. to IEC 60751

---

**Accuracy**

class A acc. to IEC 60751

class B acc. to IEC 60751

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

Thermometer

**Ex - approvals**

transmitter only

FM IS

CSA IS

FM/CSA IS

---

**Certification**

SIL (transmitter only)

---

Mais informações [www.br.endress.com/TH15](http://www.br.endress.com/TH15)