

TN analyzer

Liquiline System CA80TN

Total nitrogen analyzer for environmental monitoring, industrial and municipal wastewater



Mais informações e preço atual:

www.br.endress.com/CA80TN

Benefícios:

- Standardized alkaline persulfate digestion and UV-photometric measurement according to HJ636 offer direct comparability to most cuvette tests.
- Robust: Titanium reactor with sapphire glass windows ensures a long lifetime.
- Flexible: Integrated dilution module covers a wide measuring range.
- Fast and easy process integration: Direct installation of self-priming version or y-strainer for bypass applications.
- Easy upgrade to a complete measuring station - simply by adding modules and connecting Memosens sensors.

Especificações resumidas

- **Measurement range** 0 to 10 mg/l N 0 to 50 mg/l N 0 to 200 mg/l N
- **Process temperature** 4 to 40 °C (39.2 to 104 °F)
- **Process pressure** At atmospheric pressure, < 0.2 bar

Campo de aplicação: Nitrogen is a lead parameter to determine surface water quality and wastewater effluent values. Both, organic and inorganic substances contribute to the total nitrogen load. Increased nitrogen contents indicate influences from wastewater, landfill leachate or agriculture. Liquiline System CA80TN analyzer offers precise online measurement of total nitrogen and ensures highest process safety. Advanced diagnostics with remote access support you in providing process documentation to the authorities.

Características e especificações

Analyser

Measuring principle

UV photometric

Characteristic

Process analyzer for total nitrogen in aqueous solutions

UV photometric method following HJ636-2012

Size

Housing (open version):

793 x 530 x 417 mm

31.22 x 20.87 x 16.42 in

Housing (closed version):

793 x 530 x 463 mm

31.22 x 20.87 x 18.23 in

Housing with base:

1723 x 530 x 463 mm

67.83 x 20.87 x 18.23 in

Design

Open design, cabinet and stand housing

High-Performance plastic ASA-PC, additional stand coated steel

Process temperature

4 to 40 °C (39.2 to 104 °F)

Ambient temperature

5 to 40 °C (41 to 104 °F)

Process pressure

At atmospheric pressure, < 0.2 bar

Sample flow rate

Min. 15 ml/min (0.51 fl.oz/min)

Consistency of the sample

Aqueous, homogeneous

Analyser

Application

Monitoring of wastewater treatment plant outlet
Monitoring of the surface water quality
Monitoring of industrial water treatment
Monitoring and optimization of industrial wastewater treatment plants

Power supply

100 to 120 VAC / 200 to 240 VAC \pm 10%
50 \pm 1 or 60 \pm 1,2 Hz

Output / communication

2x 0/4 to 20 mA
Modbus RS485/TCP (optional)
Webserver (optional)
Ethernet/IP
Profibus DP
Alarm relay

Input

1 measuring channel
1 to 4 digital sensor inputs for sensors with Memosens protocol (optional)

Measurement range

0 to 10 mg/l N
0 to 50 mg/l N
0 to 200 mg/l N

Consumables

Reagents and standard solutions CY80TN as well as cleaner CY800 are necessary for the operation
Regular maintenance is done with the parts of the maintenance kit CAV880

Mais informações www.br.endress.com/CA80TN