

Proline Promass F 500 Coriolis flowmeter

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os



Mais informações e preço atual:

www.br.endress.com/8F5B

Benefícios:

- Highest process safety – immune to fluctuating and harsh environments
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in-/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Especificações resumidas

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.25\%$ Density (liquid): $\pm 0.0005\text{ g/cm}^3$
- **Measuring range** 0 to 2 200 000 kg/h (0 to 80 840 lb/min)
- **Medium temperature range** Standard: -50 to $+150\text{ }^\circ\text{C}$ ($-58\text{...}+302\text{ }^\circ\text{F}$) Option: -50 to $+240\text{ }^\circ\text{C}$ ($-58\text{...}+464\text{ }^\circ\text{F}$) High temperature option: -50 to $+350\text{ }^\circ\text{C}$ ($-58\text{...}+662\text{ }^\circ\text{F}$) Option: -196 to $+150\text{ }^\circ\text{C}$ (-320 to $+302\text{ }^\circ\text{F}$)
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022) Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Campo de aplicação: Promass F has a long-standing reputation as a highly accurate sensor. Immune to fluctuating and harsh environments it is suited for the broadest range of applications. With its innovative remote transmitter Promass F 500 maximizes installation flexibility and operational safety in demanding environments. Heartbeat Technology ensures measurement reliability and enables extension of recalibration cycles.

Características e especificações

Density

Measuring principle

Coriolis

Product Headline

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature: -196 to $350\text{ }^{\circ}\text{C}$ (-320 to $662\text{ }^{\circ}\text{F}$). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Density

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 ... $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

High temperature option: -50 to $+350$ °C (-58 ... $+662$ °F)

Option: -196 to $+150$ °C (-320 to $+302$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -60 to $+60$ °C (-76 to $+140$ °F)

Density

Sensor housing material

Standard: 1.4301 (304), corrosion resistant

Option: 1.4404 (316L)

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L);
1.4409 (CF3M) similar to 316L

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69.

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Density

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Density/Concentration

Measuring principle

Coriolis

Product headline

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature: -196 to $350\text{ }^{\circ}\text{C}$ (-320 to $662\text{ }^{\circ}\text{F}$). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Density/Concentration**Nominal diameter range**DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Measured variablesMass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement errorMass flow (liquid): ± 0.10 % (standard), 0.05 % (option)Volume flow (liquid): ± 0.10 %Mass flow (gas): ± 0.25 %Density (liquid): ± 0.0005 g/cm³

Measuring range0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressurePN 100, Class 600, 63K

Medium temperature rangeStandard: -50 to $+150$ °C (-58 ... $+302$ °F)Option: -50 to $+240$ °C (-58 ... $+464$ °F)High temperature option: -50 to $+350$ °C (-58 ... $+662$ °F)Option: -196 to $+150$ °C (-320 to $+302$ °F)

Ambient temperature rangeStandard: -40 to $+60$ °C (-40 to $+140$ °F)Option: -60 to $+60$ °C (-76 to $+140$ °F)

Density/Concentration

Sensor housing material

Standard: 1.4301 (304), corrosion resistant

Option: 1.4404 (316L)

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L);
1.4409 (CF3M) similar to 316L

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69.

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Density/Concentration**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 (Liquids other than water, Hydrocarbons, LPG, cryogenic liquids)

NTEP (Liquids other than water, LPG, cryogenic liquids)

MC (Liquids other than water, cryogenic liquids)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME,

NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Density/Concentration

Liquids

Measuring principle

Coriolis

Product headline

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error $\pm 0.05\%$ (PremiumCal). Medium temperature: -196 to $350\text{ }^{\circ}\text{C}$ (-320 to $662\text{ }^{\circ}\text{F}$). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Liquids

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to $+150$ °C (-58 ... $+302$ °F)

Option: -50 to $+240$ °C (-58 ... $+464$ °F)

High temperatur option: -50 to $+350$ °C (-58 ... $+662$ °F)

Option: -196 to $+150$ °C (-320 to $+302$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -60 to $+60$ °C (-76 to $+140$ °F)

Sensor housing material

Standard: 1.4301 (304), corrosion resistant

Option: 1.4404 (316L)

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L);

1.4409 (CF3M) similar to 316L

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Liquids

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69.

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus

RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Liquids

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 (Liquids other than water, Hydrocarbons, LPG, cryogenic liquids)

NTEP (Liquids other than water, LPG, cryogenic liquids)

MC (Liquids other than water, cryogenic liquids)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Steam

Measuring principle

Coriolis

Product headline

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Steam

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature: -196 to 350 °C (-320 to 662 °F). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Steam**Max. process pressure**PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to +150 °C (-58...+302 °F)

Option: -50 to +240 °C (-58...+464 °F)

High temperatur option: -50 to +350 °C (-58...+662 °F)

Option: -196 to +150 °C (-320 to +302 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -60 to +60 °C (-76 to +140 °F)

Sensor housing material

Standard: 1.4301 (304), corrosion resistant

Option: 1.4404 (316L)

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L);
1.4409 (CF3M) similar to 316L

Transmitter housing materialAlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69.

Transmitter remote version: IP66/67, Type 4X enclosure

External WLAN antenna: IP67

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Steam**Outputs**

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communicationHART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safetyFunctional safety according to IEC 61508, applicable in safety-relevant
applications in accordance with IEC 61511

Steam**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 (Liquids other than water, Hydrocarbons, LPG, cryogenic liquids)

NTEP (Liquids other than water, LPG, cryogenic liquids)

MC (Liquids other than water, cryogenic liquids)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

cGMP

Gas**Measuring principle**

Coriolis

Product headline

Flowmeter with premium accuracy and robustness, as remote version with up to 4 I/Os.

Highest measurement performance for liquids and gases under varying, demanding process conditions.

Gas

Sensor features

Highest process safety – immune to fluctuating and harsh environments. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

Mass flow: measurement error ± 0.05 % (PremiumCal). Medium temperature: -196 to 350 °C (-320 to 662 °F). Nominal diameter: DN 8 to 250 ($\frac{3}{8}$ to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Nominal diameter range

DN 8 to 250 ($\frac{3}{8}$ to 10")

Wetted materials

Measuring tube: 1.4539 (904L); 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022)

Connection: 1.4404 (316/316L); Alloy C22, 2.4602 (UNS N06022); 1.4301 (F304)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.25 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 840 lb/min)

Gas

Max. process pressure

PN 100, Class 600, 63K

Medium temperature range

Standard: -50 to +150 °C (-58 to +302 °F)

Option: -50 to +240 °C (-58 to +464 °F)

High temperature option: -50 to +350 °C (-58 to +662 °F)

Option: -196 to +150 °C (-320 to +302 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -60 to +60 °C (-76 to +140 °F)

Sensor housing material

Standard: 1.4301 (304), corrosion resistant

Option: 1.4404 (316L)

Sensor connection housing (standard): AISi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L);

1.4409 (CF3M) similar to 316L

Transmitter housing material

AISi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69.

Transmitter remote version: IP66/67, Type 4X enclosure

External WLAN antenna: IP67

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Gas**Outputs**

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Gas

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 (Liquids other than water, Hydrocarbons, LPG, cryogenic liquids)

NTEP (Liquids other than water, LPG, cryogenic liquids)

MC (Liquids other than water, cryogenic liquids)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Hygienic approvals and certificates

3-A, EHEDG, cGMP

Mais informações www.br.endress.com/8F5B