

RIA46

Field meter with control unit

Multifunctional field meter for monitoring and indication of analog measured values



a partir de **R\$ 8.157,89**

Preço a partir de 05.08.2021

Mais informações e preço atual:

www.br.endress.com/RIA46

Benefícios:

- 5-digit 7-segment LC display, backlit
- 1 or 2 universal inputs
- 2 relays (optional)
- Min./max. value saved
- 1 or 2 calculated values and linearization table
- Digital status output (Open Collector)
- SIL 2 approval (optional)

Especificações resumidas

- **Input** 2 x universal (U, I, R, RTD, TC)
- **Output** 2 x analogue output (I, U) 1 x loop power supply
- **Output** 2 x analogue output (I, U) 1 x loop power supply
- **Display** Multicolor backlight LCD White/black/yellow Bargraph
Unit TAG Alarm warning in plain text
- **Power Supply** 20...250V AC/DC

Campo de aplicação: Analog measured values are indicated, evaluated and calculated by the field indicator. With the integrated loop power supply two-wire sensors can be powered. The universal inputs enable the connection of current, voltage, RTDs and TCs. Limit values can be monitored and relays can be switched. Via analog outputs process signals can be forwarded. The integrated application package "differential pressure" allows the quick and easy commissioning for differential pressure applications.

Características e especificações

Process indicator & control units**Measuring principle**Indicators with control unit

Measuring principleField meter with control unit

Function

Display

Loop Power Supply

Transmitter Functionality

Barrier

Signal Isolation

Calculation

Limit Alarm

Display

Multicolor backlight LCD

White/black/yellow

Bargraph

Unit

TAG

Alarm warning in plain text

Power Supply20...250V AC/DC

Process indicator & control units**Input**

2 x universal (U, I, R, RTD, TC)

Output

2 x analogue output (I, U) 1 x loop power supply

Output

2 x analogue output (I, U) 1 x loop power supply

Software functions

Linearization

Minimum value per channel

Maximum value per channel

Calculation

Band value monitoring

Certificates

ATEX II (1) GD [Ex ia] 4C

CSA AIS

NI/I/2 ABCDEFG/T4

FM AIS

NI/I/2 ABCDEFG/T4

SIL

2

Panel mounting

field

Acquisition / Evaluation

Measuring principleDisplay

Function

Display

Loop Power Supply

Transmitter Functionality

Barrier

Signal Isolation

Calculation

Limit Alarm

Certification

ATEX II (1) GD [Ex ia] 4C

CSA AIS

NI/I/2 ABCDEFG/T4

FM AIS

NI/I/2 ABCDEFG/T4

UR C/US

Input2 x universal (U, I, R, RTD, TC)

Output

2 x analogue output (I, U)

1 x loop power supply

Acquisition / Evaluation**Relay output**

2 x changeover contact

1 x open collector

Auxiliary power supply / Loop power supply20...250V AC/DC

Dimensions (wxhxd)

Field housing:

199 x 133 x 96 mm

(7.83" x 5.24" x 3.78")

Software

Linearization

Minimum value per channel

Maximum value per channel

Calculation

Band value monitoring

Operation

3 keys

Interface CDI to USB at PC + configuration software

FieldCare

Acquisition / Evaluation

Display

Multicolor backlight LCD

White/black/yellow

Bargraph

Unit

TAG

Alarm warning in plain text

Mais informações www.br.endress.com/RIA46