

RNS221

Transmitter supply for DIN rail

Power supply for two 2 wire sensors or transmitters



Mais informações e preço atual:

www.br.endress.com/RNS221

Benefícios:

- Galvanic isolation between all circuits
- Sockets and built in 250 Ohm resistor for HART® communication
- Wide-range power supply 20 to 250 V AC/DC, 50/60 Hz
- Top hat DIN rail mounted housing to IEC 60715

Especificações resumidas

- **Output** 2 x 24 V / 30 mA Transmitter power supply

Campo de aplicação: The power supply has two galvanically isolated outputs for supplying voltage to sensors and transmitters. A built-in communication resistance enables bidirectional HART® communication with SMART sensors and transmitters.

Características e especificações

Power supplies & barrier

Measuring principle

Power supply

Measuring principle

Power supply

Function

Power supply for two 2-wire sensors or transmitters

Power supplies & barrier

Loop power supply

20...250 V AC

20...250 V DC

Auxiliary power supply / Loop power supply

20...250 V AC

20...250 V DC

Output

2 x 24 V / 30 mA

Transmitter power supply

Operation

HART

Acquisition / Evaluation

Measuring principle

Power supply

Function

Power supply for two 2-wire sensors or transmitters

Certification

-

Output

2 x 24V / 30mA

Transmitter power supply

Auxiliary power supply / Loop power supply

20...250 V AC

20...250 V DC

Acquisition / Evaluation

Dimensions (wxhxd)

22.5 x 110 x 112 mm

(0.89" x 4.33" x 4.41")

Operation

HART

Mais informações www.br.endress.com/RNS221