

Vibronic

Point level detection

Liquiphant FTL33

Point level switch for liquids in compact
hygienic design for the food industry



from **CA\$329.00**

Price as of 28.11.2022

More information and current pricing:

www.ca.endress.com/FTL33

Benefits:

- Designed for hygienic applications especially in the food industry - hygienic process connections and approvals available. IO-Link reduces costs and complexity due to easy configuration of the devices via engineering tools
- CIP and SIP cleanability ensured - up to protection class IP69k
- Designed according to highest requirements to quality and environmental sustainability, the self-monitoring Liquiphant offers safe switching also in case of power supply loss
- Independent of changing media properties an accurate switching point is offered
- A real plug & play sensor is offered without any need for adjustment even with changing media. Measurement is unaffected by conductivity, build-up, turbulence, flows or air bubbles
- No calibration is required, no specific know-how or tools (e.g. software) necessary
- Robust design made of stainless steel (316L) assures highest durability - no mechanically moved parts, free of maintenance

Specs at a glance

- **Process temperature** -40 °C ... 150 °C (-40 °F ... 302 °F)
- **Process pressure / max. overpressure limit** Vacuum ... 40 bar (Vacuum ... 580 psi)
- **Min. density of medium** >0,7g/cm³ (>0,5g/cm³ optional)

Field of application: Liquiphant FTL33 is a point level switch for liquids. The FTL33 is especially designed for food & beverage applications where hygienic requirements are requested. The Liquiphant is used for overfill

prevention or pump dry-run protection. The IO-Link capability allows easy parameter setting. **Compact:** - Smallest vibronic sensor in the market **Safe:** - Continuous self-monitoring - Reliable switching independent of media properties **Easy:** - No calibration - Plug & play -IO-Link connectivity

Features and specifications

Point Level / Liquids

Measuring principle

Vibration Liquids

Characteristic / Application

Point level switch for liquids
in the food sector

Supply / Communication

20 ... 253V AC/DC, 2-wire
10 ... 30V DC-PNP, 3-wire

Ambient temperature

40 °C ... 70 °C
(-40 °F ... 158 °F)

Process temperature

-40 °C ... 150 °C
(-40 °F ... 302 °F)

Process pressure / max. overpressure limit

Vacuum ... 40 bar
(Vacuum ... 580 psi)

Min. density of medium

>0,7g/cm³
(>0,5g/cm³ optional)

Main wetted parts

316L

Point Level / Liquids

Process connection

Threads:

G1/2, G3/4, G1, MNPT1/2, MNPT3/4, MNPT1, R1/2, R3/4, R1

Process connection hygienic

Flush mount by use of weld in adapter

DIN11851

Tri-Clamp

Communication

AC/DC, DC-PNP, IO-Link

Certificates / Approvals

CSA C/US, EAC

Safety approvals

Overfill protection WHG

Leakage

Design approvals

EN 10204-3.1

Hygienic approvals

3A, EHEDG

Options

Switching delay

Cleaned from oil+grease,

Surface finish measurement

More information www.ca.endress.com/FTL33