

Proline Promass O 300 Coriolis flowmeter

Robust high-pressure flowmeter with a compact, easily accessible transmitter



F L E X

Benefits:

- Maximum safety – highest resistance to stress corrosion cracking
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ (standard), 0.05% (option) Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.35\%$ Density (liquid): $\pm 0.0005\text{ g/cm}^3$
- **Measuring range** 0 to 800 000 kg/h (0 to 29 400 lb/min)
- **Medium temperature range** -40 to $+205\text{ }^\circ\text{C}$ (-40 to $+401\text{ }^\circ\text{F}$)
- **Max. process pressure** PN 250, Class 1500
- **Wetted materials** Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750) Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

More information and current pricing:

www.ca.endress.com/803B

Field of application: Promass O is designed for premium accuracy of liquids and gases at the highest process pressures in the oil and gas industry. The sensor is fully suitable for offshore conditions and resistant to stress corrosion cracking. With its compact transmitter Promass O 300 offers high flexibility in terms of operation and system integration: access from one side, remote display and improved connectivity options. Heartbeat Technology ensures safe processes.

Features and specifications

Liquids

Measuring principle

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs. Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 250 (3 to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 250 (3 to 10")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Liquids

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 850 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Liquids

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Liquids

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK"

Gas

Measuring principle

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 250 (3 to 10").

Gas

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 250 (3 to 10")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 2 200 000 kg/h (0 to 80 850 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Gas

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)
Configuration via local display and operating tools possible
Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Gas

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Steam

Measuring principle

Coriolis

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Steam

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs. Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 250 (3 to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 150 (3 to 6")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)
Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 800 000 kg/h (0 to 29 400 lb/min)

Max. process pressure

PN 250, Class 1500

Steam**Medium temperature range**

–40 to +205 °C (–40 to +401 °F)

Ambient temperature range

Standard: –40 to +60 °C (–40 to +140 °F)

Option: –50 to +60 °C (–58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4–20 mA HART (active/passive)

4–20 mA WirelessHART

4–20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4–20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus

RS485, Profinet, Ethernet/IP, OPC-UA

Steam**Power supply**

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK

Density/Concentration**Measuring principle**

Coriolis

Density/Concentration

Product headline

Robust high-pressure flowmeter with a compact, easily accessible transmitter.

For premium accuracy at highest process pressures, fully suitable for offshore conditions.

Sensor features

Maximum safety – highest resistance to stress corrosion cracking. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Measuring tube in 25Cr Duplex, 1.4410 (UNS S32750). Process pressure up to PN 250 (Class 1500). Nominal diameter: DN 80 to 250 (3 to 10").

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 80 to 250 (3 to 10")

Wetted materials

Measuring tube: 25Cr duplex (Super Duplex), 1.4410 (UNS S32750)

Connection: 25Cr duplex (Super Duplex), 1.4410 (F53)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow (API tables), reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 % (standard), 0.05 % (option)

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.35 %

Density (liquid): ± 0.0005 g/cm³

Density/Concentration**Measuring range**

0 to 2 200 000 kg/h (0 to 80 850 lb/min)

Max. process pressure

PN 250, Class 1500

Medium temperature range

-40 to +205 °C (-40 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4404 (316L), highest corrosion resistance

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

Outputs

3 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Density/Concentration

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

MI-005 Liquids other than water (Hydrocarbons)

MI-002, PTB

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval, CCS approval

Pressure approvals and certificates

PED, CRN, AD 2000

Material certificates

3.1 material

NACE MR0175/MR0103, PMI; welding test acc. to EN ISO, ASME, NORSOK"

More information www.ca.endress.com/803B