

Hydrostatic Level measurement Waterpilot FMX21

Reliable and robust level probe with ceramic measuring cell and HART



Benefits:

- Robust overload-resistant high purity ceramic sensor (99.9% Al₂O₃)
- Flexible scaling of 4 to 20mA with superimposed HART 6.0 output
- Highest level accuracy using temperature compensated density correction
- Simultaneous measurement of level and temperature with optionally integrated Pt100 temperature sensor
- Extensive range of accessories provides complete measuring point solutions
- Climate proofed sensor thanks to completely potted electronics and 2-filter pressure compensation system
- Small outer diameter of 22mm (0.87") version suitable for drinking water applications and for use in bore holes and wells with small diameters

More information and current pricing:

www.casc.endress.com/FMX21

Specs at a glance

- **Accuracy** 0.2% 0.1% (optional)
- **Process temperature** -10°C...70°C (14°F...158°F) Diameter 29 mm (1.14"): 0°C...50°C (32°F...122°F)
- **Pressure measuring range** 100 mbar...20 bar (1.5 psi...300 psi)
- **Main wetted parts** Diameter 22 mm and 42 mm: Seal, 316L, Ceramic Diameter 29 mm: Seal, PPS, Polyolefin, Ceramic
Extension cable: PE, PUR, FEP
- **Max. measurement distance** 200 m H₂O (656 ft H₂O)

Field of application: The Waterpilot FMX21 transmitter with capacitive, oil-free ceramic measuring cell is typically used in the process and environmental applications for hydrostatic level measurement. With

HART output, the measuring ranges can be freely adjusted and a density-compensated level measurement can be activated. It is certified for drinking water and offers integrated temperature measurement. Versions for applications in wastewaters and sludges or usage in salt water are also available.

Features and specifications

Pressure

Measuring principle

Hydrostatic pressure

Characteristic

Compact probe with ceramic cell for hydrostatic level measurement,

Diameter = 22 mm: General applications, fresh water

Diameter = 42 mm: Waste water applications

Diameter = 29 mm: Salt water applications

Supply voltage

10.5 ...35V DC

Reference Accuracy

0.2%

0.1% (optional)

Long term stability

0.1% of URL/year

Process temperature

-10°C...70°C

(14°F...158°F)

Diameter 29 mm (1.14"): 0°C...50°C

(32°F...122°F)

Pressure**Ambient temperature**

-10°C...70°C
(14°F...158°F)
Diameter 29 mm (1.14"):
0°C...50°C
(32°F...122°F)

Measuring cell

100mbar...20bar
(1.5psi...300psi)

Process connection

Suspension clamp
Cable mounting screws

Communication

4...20 mA
4...20 mA HART

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI

Marine approvals

GL/ ABS/ BV/ DNV/ LR

Drinking water approvals

NSF/ KTW/ ACS

Continuous / Liquids**Measuring principle**

Hydrostatic

Characteristic / Application

Compact probe with ceramic cell for hydrostatic level measurement,
Diameter = 22 mm: General applications, Fresh water
Diameter = 42 mm: Waste water applications
Diameter = 29 mm: Salt water applications

Continuous / Liquids

Specialities

Automatic density compensation
Version w/o metal parts in contact to process

Supply / Communication

10.5 ...35 VDC

Accuracy

0.2%
0.1% (optional)

Long term stability

0.1% of URL/year

Ambient temperature

-10°C...70°C
(14°F...158°F)
Diameter 29 mm (1.14"):
0°C...50°C
(32°F...122°F)

Process temperature

-10°C...70°C
(14°F...158°F)
Diameter 29 mm (1.14"): 0°C...50°C
(32°F...122°F)

Pressure measuring range

100 mbar...20 bar
(1.5 psi...300 psi)

Main wetted parts

Diameter 22 mm and 42 mm: Seal, 316L, Ceramic
Diameter 29 mm: Seal, PPS, Polyolefin, Ceramic
Extension cable: PE, PUR, FEP

Continuous / Liquids

Process connection

Suspension clamp
Cable mounting screws

Max. measurement distance

200 m H₂O
(656 ft H₂O)

Communication

4...20 mA
4...20 mA HART

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, NEPSI

Marine approval

GL/ ABS/ BV/ DNV/ LR

Drinking water approvals

KTW/ NSF/ ACS

Options

Absolute measuring cell
Integrated temperature sensor Pt100, 4-wire
customer specific adjustment
customer specific cable marking

Application limits

Measuring cell: ceramics

More information www.casc.endress.com/FMX21