

# Ultrasonic measurement Time-of-Flight Prosonic FMU41

Cost effective device for sophisticated level measurement in liquids and bulk solids for up to 8m



More information and current pricing:

[www.casc.endress.com/FMU41](http://www.casc.endress.com/FMU41)

## Benefits:

- Reliable non-contact measurement
- Quick and simple commissioning via menu-guided on-site operation with four-line plain text display, 7 languages selectable
- Envelope curves on the on-site display for simple diagnosis
- Hermetically sealed and potted sensor
- Chemically resistant sensor out of PVDF
- Calibration without filling or discharging
- Integrated temperature sensor for automatic correction of the temperature dependent sound velocity

## Specs at a glance

- **Accuracy** +/- 2 mm or +/- 0,2 % of set measuring range 1)
- **Process temperature** -40 °C ... 80 °C (-40 °F ... 176 °F)
- **Process pressure absolute / max. overpressure limit** 0.7 bar ... 3 bar abs (10 psi ... 44 psi)
- **Max. measurement distance** 3.5 m (11 ft)
- **Main wetted parts** PVDF

**Field of application:** The Prosonic FMU41 sensor is suited for non-contact level measurement in fluids, pastes, coarse bulk material and flow measurement in open channels or at weirs. The two-wire or four-wire compact transmitter can be used in applications with storage tanks, agitators, on stockpiles and conveyor belts. The envelope curve can be shown on the on-site display for simple diagnosis. Linearization function

(up to 32 points) for conversion of the measured value into any unit of length, volume or flow rate.

## Features and specifications

### Continuous / Solids

**Measuring principle**

Ultrasonic

**Characteristic / Application**

Compact ultrasonic transmitter

**Supply / Communication**

2/4-wire (HART), PROFIBUS PA, FOUNDATION  
Fieldbus

**Accuracy**

+/- 2 mm or +/- 0,2 % of set measuring range 1)

**Ambient temperature**

-40 °C ... 80 °C  
(-40 °F ... 176 °F)

**Process temperature**

-40 °C ... 80 °C  
(-40 °F ... 176 °F)

**Process pressure absolute / max. overpressure limit**

0.7 bar ... 3 bar abs  
(10 psi ... 44 psi)

**Main wetted parts**

PVDF

**Process connection**

G / NPT 2"

**Blocking distance**

0.35 m (1.15 ft)

---

**Continuous / Solids****Max. measurement distance**3.5 m (11 ft)

---

**Communication**4 ... 20 mA HART  
PROFIBUS PA  
FOUNDATION Fieldbus

---

**Certificates / Approvals**ATEX, FM, CSA, TIIS, INMETRO, NEPSI

---

**Application limits**Take notice of range diagram

---

**Liquids****Measuring principle**Ultrasonic

---

**Product headline**Compact ultrasonic measuring  
instrument  
Cost effective solution for open channels

---

**Max. measurement error**Low accuracy

---

**Measuring range**Measuring distance 0,4...8m [1.3...26ft]

---

**Max. process pressure**atm.

---

**Medium temperature range**-40°C...80°C  
(-40°F...176°F)

---

**Degree of protection**IP68

---

---

**Liquids****Outputs**4...20mA(Hart),PA,FF

---

**Inputs**

2-wire 16-36V DC

4-wire 16-36V DC

90-253V AC 50/60Hz

---

**Digital communication**PROFIBUS PA, FOUNDATION Fieldbus

---

**Hazardous area approvals**ATEX, FM, CSA

---

**Continuous / Liquids****Measuring principle**Ultrasonic

---

**Characteristic / Application**Compact ultrasonic transmitter

---

**Supply / Communication**2/4-wire (HART), PROFIBUS PA, FOUNDATION  
Fieldbus

---

**Accuracy**+/- 2 mm or +/- 0,2 % of set measuring range

---

**Ambient temperature**

-40 °C ... 80 °C

(-40 °F ... 176 °F)

---

**Process temperature**

-40 °C ... 80 °C

(-40 °F ... 176 °F)

---

---

**Continuous / Liquids****Process pressure absolute / max. overpressure limit**

0.7 bar ... 3 bar abs  
(10 psi ... 44 psi)

---

**Main wetted parts**

PVDF

---

**Process connection**

G / NPT 2"

---

**Blocking distance**

0.35 m (1.15 ft)

---

**Application**

Application

---

**Max. measurement distance**

Max. measurement distance

---

**Communication**

4 ... 20 mA HART  
PROFIBUS PA  
FOUNDATION Fieldbus

---

**Certificates / Approvals**

ATEX, FM, CSA, TIIS, INMETRO, NEPSI

---

**Application limits**

Application limits

---

More information [www.casc.endress.com/FMU41](http://www.casc.endress.com/FMU41)