

# 8-channel transmitter

## Liquiline CM448

### Flexible multiparameter field device for all industries



More information and current pricing:

[www.ch.endress.com/CM448](http://www.ch.endress.com/CM448)

#### Benefits:

- **Clever simplicity:**  
One controller for all parameters and applications, intuitive user interface, automatic sensor recognition, hot plug & play with pre-calibrated Memosens sensors.
- **Complete package:**  
8 channels in one device provide the highest flexibility for every measuring task.
- **Seamless system integration:**  
Unique portfolio of communication standards suits every distributed control system (DCS).
- **Simple and safe commissioning:**  
Saving configuration on SD card enables fast set-up on duplicate installations.
- **Process control from a distance:**  
Integrated web server that allows the operator to remotely view diagnostic data, perform configurations, or access device parameters in any web browser - even via Smartphone.
- **Higher availability, lower costs:**  
Heartbeat Technology enables status-oriented maintenance and easy verification of the entire measuring point and helps to carry out optimization measures.

#### Specs at a glance

- **Input** 1 to 8x Memosens digital input 2x 0/4 to 20mA Input optional 2 to 4x Digital input optional

**Output / communication** 2 to 8x 0/4 to 20 mA current outputs, alarmrelay 4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

- **Ingres protection** IP66 / IP67

**Field of application:** The Liquiline CM448 transmitter allows you to connect up to 8 Memosens sensors of your choice from over 12 measurement parameters. It offers automatic sensor recognition, simple operation, and standardized spare parts with all other devices of the Liquiline platform. With its inputs, outputs, controllers, and math modules, you can even control cleaning systems or dosing pumps. Heartbeat Technology helps you find the ideal balance between measuring point availability and maintenance costs.

## Features and specifications

### Conductivity

#### Measuring principle

Conductive

#### Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

#### Characteristic

Robust plastic housing

All non-ex applications

#### Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

**Conductivity****Material**

Housing base: PC-FR

Housing seal EPDM

---

**Dimension**

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

---

**Ingres protection**

IP66 / IP67

---

**Input**

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

**ORP / Redox****Measuring principle**

Sensor ORP / Redox

---

**Application**

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

## ORP / Redox

**Characteristic**

Robust plastic housing  
All non-ex applications

---

**Design**

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of  
setup

---

**Material**

Housing base: PC-FR  
Housing seal EPDM

---

**Dimension**

237 x 194 x 162 mm  
9.33 x 7.64 x 6.38 inch

---

**Process temperature**

-20 to 55 °C (0 to 130 °F)

---

**Ingres protection**

IP66 / IP67

---

**Input**

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

## Disinfection

**Measuring principle**

Free chlorine

---

## Disinfection

### Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

### Characteristic

Robust plastic housing

All non-ex applications

### Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

### Material

Housing base: PC-FR

Housing seal EPDM

### Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

### Process temperature

-20 to 55 °C (0 to 130 °F)

### Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

### Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Disinfection****Additional certifications**EAC, cCSAus

---

**Analyser****Measuring principle**Potentiometric / ISE

---

**Characteristic**Robust plastic housing  
All non-ex applications

---

**Process temperature**-20 to 55 °C (0 to 130 °F)

---

**Application**Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

**Output / communication**2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Input**1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

**Oxygen****Measuring principle**Amperometric oxygen measurement

---

## Oxygen

### Application

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

### Characteristic

Robust plastic housing

All non-ex applications

### Design

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

### Material

Housing base: PC-FR

Housing seal EPDM

### Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

### Process temperature

-20 to 55 °C (0 to 130 °F)

### Input

1 to 8x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

### Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

Oxygen

**Additional certifications**

EAC, cCSAus

---

pH

**Measuring principle**

Potentiometric

---

**Application**

Modular 4 wire controller

Multichannel: 1 to 8 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

8 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

---

**Characteristic**

Robust plastic housing

All non-ex applications

---

**Design**

8x Memosens input, 2 to 8x current output,

Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

**Material**

Housing base: PC-FR

Housing seal EPDM

---

**Dimension**

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

---

**Process temperature**

-20 to 55 °C (0 to 130 °F)

---

**Ingres protection**

IP66 / IP67

---



---

**pH****Input**

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

**Turbidity****Measuring principle**

Single beam scattered light

---

**Application**

Modular 4 wire controller  
Multichannel: 1 to 8 digital channels for Memosens protocol  
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity  
8 sensors connectable in any combination  
Functionality modular extendable at any time  
Plug and play for modules and sensors

---

**Characteristic**

Robust plastic housing  
All non-ex applications

---

**Design**

8x Memosens input, 2 to 8x current output,  
Alarmrelay, 2x relay, SD card for software update and copy & paste of setup

---

**Material**

Housing base: PC-FR  
Housing seal EPDM

---

## Turbidity

**Dimension**

237 x 194 x 162 mm  
9.33 x 7.64 x 6.38 inch

---

**Process temperature**

-20 to 55 °C (0 to 130 °F)

---

**Ingres protection**

IP66 / IP67

---

**Input**

1 to 8x Memosens digital input  
2x 0/4 to 20mA Input optional  
2 to 4x Digital input optional

---

**Output / communication**

2 to 8x 0/4 to 20 mA current outputs, alarmrelay  
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

---

**Additional certifications**

EAC, cCSAus

---

More information [www.ch.endress.com/CM448](http://www.ch.endress.com/CM448)