

Manual or automatic retractable assembly Cleanfit CPA473

Assembly with ball valve for the chemical, paper, and wastewater industries



More information and current pricing:

www.ch.endress.com/CPA473

Benefits:

- Safe and reliable separation from the process by ball valve, even under harsh conditions
- No process interruption for electrode cleaning and calibration – saves maintenance time and costs
- Extended operating life of electrodes due to automatic cleaning
- Suitable for application in sticky and fibrous media thanks to integrated scraper and sleeve seals
- Flexible adaptation to all applications by great variety of materials and process connections

Specs at a glance

- **Process temperature** PA pressure cylinder (manually only): Max. 80 °C (176 °F) Stainless steel pressure cylinder: up to 100°C (212 °F) with continuous operation up to 6 bar (87 psi)
- **Process pressure** PA pressure cylinder: Max. 6 bar (87 psi) Stainless steel pressure cylinder: Max. 10 bar (145 psi) Pneumatic outlet safety seal: 6 bar at 100 °C (87 psi at 212 °F)

Field of application: The Cleanfit CPA473 retractable assembly is designed for application in fibrous or sticky media. Its patented sleeve seals and integrated scrapers make sure that nothing sticks to the sensor. Cleanfit offers highest operating comfort: You can replace sensors and even service the assembly while the process is running. The optional electric or pneumatic control system enables automated cleaning and calibration even in difficult processes.

Features and specifications

pH

Measuring principle

Potentiometric

Application

Chemical industry, paper industry, wastewater, industrial water, power plants, refuse incinerators, sugar industry

Installation

Retractable assembly with ball valve

Characteristic

Open and closed tank, piping (min DN80)

Design

Manual or pneumatical

Manual or pneumatical ball valve

Can be fully automated with CPC30 / 300

Integrated rinse chamber with connection G 1/4" or NPT 1/4"

Material

Seals: EPDM / FPM / perfluoroelastomer

Electrode holder: stainless steel 1.4404

Ball valve: Stainless steel 1.4401, PTFE

Inlet safety seal: PVDF, PTFE, Viton®

Outlet safety seal: PVDF, Stainless steel 1.4404

Rinse connection socket: Stainless steel 1.4404

Dimension

Immersion depth: 61 to 235mm

(2.4 inch to 9.25 inch)

Process temperature

PA pressure cylinder (manually only):

Max. 80 °C (176 °F)

Stainless steel pressure cylinder: up to 100°C (212 °F) with continuous operation up to 6 bar (87 psi)

pH

Process pressure

PA pressure cylinder: Max. 6 bar (87 psi)

Stainless steel pressure cylinder: Max. 10 bar (145 psi)

Pneumatic outlet safety seal:

6 bar at 100 °C (87 psi at 212 °F)

Connection

G1¼ internal thread, DN50, DN65, ANSI 2"

Additional certifications

3.1. acc. to EN 10204

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Chemical industry, paper industry, wastewater, industrial water, power plants, refuse incinerators, sugar industry

Installation

Retractable holder with ball valve

Characteristic

Open and closed tank, piping (min DN80)

Design

Manual or pneumatical

Manual or pneumatical ball valve

Can be fully automated with CPC30 / 300

Integrated rinse chamber with connection G 1/4" or NPT 1/4"

ORP / Redox

Material

Seals: EPDM / FPM / perfluoroelastomer

Electrode holder: stainless steel 1.4404

Ball valve: Stainless steel 1.4401, PTFE

Inlet safety seal: PVDF, PTFE, Viton®

Outlet safety seal: PVDF, Stainless steel 1.4404

Rinse connection socket: Stainless steel 1.4404

Dimension

Immersion depth: 61 to 235mm

(2.4 inch to 9.25 inch)

Process temperature

PA pressure cylinder (manually only):

Max. 80 °C (176 °F)

Stainless steel pressure cylinder:

up to 100°C (212 °F) with continuous operation up to 6 bar (87 psi)

Process pressure

PA pressure cylinder: Max. 6 bar (87 psi)

Stainless steel pressure cylinder: Max. 10 bar (145 psi)

Pneumatic outlet safety seal:

6 bar at 100 °C (87 psi at 212 °F)

Connection

G1¼ internal thread, DN50, DN65, ANSI 2"

Additional certifications

3.1.B EN 10204

More information www.ch.endress.com/CPA473